

SAISWP-M-4D-4/8-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Male plugs and female socket for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M12 plug-in connectors offer a choice of 5 different connection systems.

General ordering data

Version	Field attachable connector, M12
Order No.	2681690000
Type	SAISWP-M-4D-4/8-M12
GTIN (EAN)	4050118759860
Qty.	1 items

SAISWP-M-4D-4/8-M12

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E307231

Dimensions and weights

Diameter	19 mm	Net weight	40 g
----------	-------	------------	------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data customisable plug-in connectors

Number of poles	4	Coding	D-coded
Contact surface	Ni/Au	LED	No
Type of connection	PUSH IN	Housing main material	PA 66
Insulation resistance	≥ 100 MΩ	Cable diameter, max.	8 mm
Cable diameter, min.	4 mm	Category	Cat.5 (ISO/IEC 11801)
Conductor cross-section, max.	0.75 mm ²	Conductor cross-section, min.	0.14 mm ²
Nominal voltage	60 V	Nominal current	4 A
Protection degree	IP67	Plugging cycles	≥ 100
Pollution severity	3	Gender of contact	Male
Shield connection	Yes	Threaded ring material	Diecast zinc

General Info

Number of poles	4	Connection 1	M12
Connection 2	PUSH IN	Wiring	4-core, PROFINET
UL 94 flammability rating	V-0	Housing main material	PA 66
Category	Cat.5 (ISO/IEC 11801)	Connection thread	M12
Contact surface	Ni/Au	Wire connection cross section, finely stranded, min.	0.14 mm ²
Wire connection cross section, finely stranded, max.	0.75 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.08 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	0.5 mm ²	Wire cross-section, solid, min.	0.14 mm ²
Wire cross-section, solid, max.	0.75 mm ²	Protection degree	IP67
Plugging cycles	≥ 100		

Electrical properties

Insulation resistance	≥ 100 MΩ	Nominal voltage	60 V
-----------------------	----------	-----------------	------

General standards

Certificate no. (cULus)	E307231
-------------------------	---------

SAISWP-M-4D-4/8-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Standards**

Fire safety for railway vehicles	DIN EN 45545-2	Shock and vibration proof according to	EN 50155:2001, DIN EN 61373
----------------------------------	----------------	--	-----------------------------

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		


SAISWP-M-4D-4/8-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Drawing



Pole scheme

