

**SAIBGS-P-5L-8/13-M12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Drawing**

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

Version	Field attachable connector, M12
Order No.	<a href="#">2703520000</a>
Type	SAIBGS-P-5L-8/13-M12
GTIN (EAN)	4050118716214
Qty.	1 items

**SAIBGS-P-5L-8/13-M12**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E307231

**Dimensions and weights**

Net weight	50.37 g
------------	---------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1

**Technical data customisable plug-in connectors**

Number of poles	5	Coding	L-coded
Contact surface	Au (Gold)	Type of connection	Screw connection
Housing main material	PA	Cable diameter, max.	13 mm
Cable diameter, min.	8 mm	Contact material	CuZn
Nominal voltage	63 V	Nominal current	16 A
Protection degree	IP67	Plugging cycles	≥ 100
Pollution severity	3	Gender of contact	Female
Threaded ring material	Diecast zinc	Temperature range of housing	-40 ... +85 ° C
Connection cross-section, max.	2.5 mm <sup>2</sup>		

**General Info**

Number of poles	5	Connection 1	M12
Connection 2	Screw	Housing main material	PA
Connection thread	M12	Contact material	CuZn
Contact surface	Au (Gold)	Wire connection cross section, finely stranded, max.	2.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm <sup>2</sup>	Protection degree	IP67
Plugging cycles	≥ 100		

**Classifications**

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

Pole scheme

