

## IE-FPOD2UG0010MSDESDEX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5, 6 and 14
- consistently Cat. 6A with STEADYTEC® technology
- in IP20 and IP67
- all relevant industrial connections: RJ45, SC, ...
- comprehensive range of accessories

### General ordering data

Version	Dragline cable, SC IP 67 PushPull V14 metal, SC IP 67 PushPull V14 metal, 980 µm, PUR, 10 m
Order No.	<a href="#">2703680100</a>
Type	IE-FPOD2UG0010MSDESDEX
GTIN (EAN)	4050118716238
Qty.	1 items

**IE-FPOD2UG0010MSDESDEX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

ROHS Conform

**Dimensions and weights**

Length	10 m	Length (inches)	393.7008 inch
Net weight	447 g		

**Temperatures**

Storage temperature	Operating temperature
Installation temperature	

**Environmental Product Compliance**

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

**Fibre-optic**

Fibre type	POF	Attenuation	≤ 160 dB/km at 650 nm
Bandwidth	> 35 MHz*100 m at 650 nm		

**Cable structure**

Material sheath	PUR	Cable layout	Break-out dragline
Primary coating	245.00 µm	Core diameter	980 µm

**Classifications**

ETIM 8.0	EC002607	ETIM 9.0	EC002607
ETIM 10.0	EC002607	ECLASS 14.0	27-06-10-03
ECLASS 15.0	27-06-10-03		