


IE-SW-AL06LM-4TX-2SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmuller.com



Features of AdvancedLine managed Switch series

Industrial networks require a future-proof infrastructure with high availability, reliability, and transparency. Managed switches increase network availability utilizing redundancies and control mechanisms as well as network diagnostics in demanding automation networks.

- Extensive set of management features enable the set-up of various redundancy, monitoring, traffic filter and security functions
- Huge variety of port count and media type enable a wide range of applications (5 to 24 ports)
- Models supporting Gigabit Ethernet including Jumbo Frame support for applications with high demand on bandwidth and latency
- Suitable for use in harsh industrial environment thanks to rugged design and wide operating temperature range of -40°C up to 75°C
- Layer 3 model for hardware supported routing between up to 20 IP-subnets

General ordering data

| | |
|------------|---|
| Version | Network switch, lite managed, Fast Ethernet, Number of ports: 4 x RJ45, 2 * SC Multi-mode, IP30, -40 °C...75 °C |
| Order No. | 2682260000 |
| Type | IE-SW-AL06LM-4TX-2SC |
| GTIN (EAN) | 4050118692457 |
| Qty. | 1 items |

IE-SW-AL06LM-4TX-2SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



| | |
|-------------------------|----------------------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate no. (cULus) | E141197 |

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 107.1 mm | Depth (inches) | 4.2165 inch |
| Height | 145.4 mm | Height (inches) | 5.7244 inch |
| Width | 54.2 mm | Width (inches) | 2.1339 inch |
| Net weight | 799 g | | |

Temperatures

| | | | |
|---------------------|----------------------------|-----------------------|----------------|
| Storage temperature | -40 °C...85 °C | Operating temperature | -40 °C...75 °C |
| Humidity | 5 to 95 % (non-condensing) | | |

Environmental Product Compliance

| | |
|--------------------------------------|---|
| RoHS Compliance Status | Compliant with exemption |
| RoHS Exemption (if applicable/known) | 7a, 7cl |
| REACH SVHC | Lead 7439-92-1, Lead monoxide 1317-36-8 |
| SCIP | 9229992a-00b9-4096-8962-200a7f33e289 |

EMC conformity and approvals

| | | | |
|-----------------|--|---------------|---|
| Free fall | According to IEC 60068-2-31 | EMC standards | EN 55032, EN 55024, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 4 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz bis 1 Ghz: 3 V/m, IEC 61000-4-4 EFT: Power: 0.5 kV; Signal: 0.5 kV, IEC 61000-4-5 Surge: Power: 1 kV; Signal: 1 kV, IEC 61000-4-6 CS: 3 Vrms |
| Vibration | according to IEC 60068-2-6 | Shock | according to IEC 60068-2-27 |
| Safety standard | SELV according to EN 62368-1, UL 61010-1, UL 61010-2-201 | | |

Environmental conditions

| | | |
|-----------------------------|----------------------------|-----------------|
| Operating temperature, max. | 75 °C | |
| Operating temperature, min. | -40 °C | |
| Humidity | 5 to 95 % (non-condensing) | |
| Storage temperature, max. | 85 °C | |
| Storage temperature, min. | -40 °C | |
| Operating altitude | Altitude, max. | 2000 m |
| | Note | in acc. with UL |
| | Altitude, max. | 6000 m |

IE-SW-AL06LM-4TX-2SC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Note

for restrictions, see the manufacturer's declaration for operating altitude in section downloads

Fibre optic transceiver characteristics

| | | |
|-----------------------------|------------|-----------|
| Transmission rate | 100 MBit/s | |
| Transceiver type | Multimode | |
| Connector type | SC-Duplex | |
| Transmission distance, typ. | 2 km | |
| Wavelength | typ. | 1310 nm |
| Receive power | min. | -31 dBm |
| | max. | 0 dBm |
| Transmission power | min. | -23.5 dBm |
| | max. | -14 dBm |
| Link-budget | 7.5 dB | |

Guarantee

| | |
|---------------|---------|
| Time interval | 5 years |
|---------------|---------|

Interfaces

| | | | |
|-----------------------|--|-----------------|---|
| Fibre-optic ports | 100BaseFX ports (SC connector), Multimode | RJ45 ports | 10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port |
| Alarm contact | 1 relay output with a current capacity of 1 A at 24 V DC | Number of ports | 4 x RJ45, 2 * SC Multimode |
| Function reset button | <5 sec: System reboot, >5 sec: Factory default | | |

MTBF

| | | |
|------|------------------------------|------------------|
| MTBF | According to Standard | Telcordia SR-332 |
| | Operating time (hours), min. | 595597 h |

Management features

| | | | |
|-----------------------|---|------------------------|--|
| Device configuration | Webbrowser (HTTP/HTTPS), SNMP v1/v2c/v3, Upload of a configuration file via web-interface or TFTP-Server, Command Line Interface (Telnet/SSH) | Monitoring function | SNMP v1/v2c/v3, Link Layer Discovery Protocol (LLDP), Syslog, Event based warning via E-Mail, Event based warning via relay, Event based warning via SNMP trap |
| Network redundancy | Spanning Tree Protocol (STP), Rapid Spanning Tree Protocol (RSTP), O-Ring (recovery time <10 ms), O-Chain (recovery time <10 ms), Fast recovery | Network traffic filter | Port based VLAN |
| IP-address management | Static, DHCP-Client, DHCP-Server (port based, pool-based), DHCP Option 82, DHCP-Relay, IPv4/IPv6 | Security functions | VLAN segmentation, Enable/disable ports, Loop protection, TACACS + Authentication, Management access security via secure IP-list and configuration of |

IE-SW-AL06LM-4TX-2SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|---------------------------------|-------------------------|-----------------------------|--|
| Time synchronization management | NTP server, SNTP client | Industrial protocol support | allowed access methods (web-interface, telnet, SSH) Modbus/TCP slave |
|---------------------------------|-------------------------|-----------------------------|--|

Power supply

| | | | |
|-----------------------------|-----------------------------------|--------|--|
| Reverse polarity protection | Yes | | |
| Supply voltage | 12/24/48 V DC, 2 redundant inputs | | |
| Overload current protection | Yes | | |
| Connection type | 1 removable 7-pin terminal block | | |
| Voltage supply range | Voltage type | DC | |
| | Voltage, min. | 10.8 V | |
| | Voltage, max. | 52.8 V | |
| Current consumption | Voltage | 12 V | |
| | Current | 0.47 A | |
| | Voltage | 24 V | |
| | Current | 0.24 A | |
| | Voltage | 48 V | |
| | Current | 0.12 A | |

Switch characteristics

| | | | |
|---------------------|------------|--------------------|--------|
| MAC table size | 2 K | Packet buffer size | 1 Mbit |
| Bandwidth backplane | 1.2 Gbit/s | | |

Technical data

| | | | |
|-----------------------|--------------|------------------|---------------|
| Housing main material | Metal | Type of mounting | DIN rail |
| Protection degree | IP30 | Speed | Fast Ethernet |
| Switch | lite managed | | |

Technology

| | | | |
|----------------|---|--------------|--------------------------|
| Data switching | Store and Forward | Flow control | IEEE 802.3x flow control |
| Standard | IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X) and 100BaseFX, IEEE 802.3x for flow control, IEEE 802.1D for the Spanning Tree protocol, IEEE 802.1w for Rapid STP, IEEE 802.1AB for Link Layer Discovery protocol (LLDP) | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000734 | ETIM 9.0 | EC000734 |
| ETIM 10.0 | EC000734 | ECLASS 14.0 | 19-17-04-01 |
| ECLASS 15.0 | 19-17-04-01 | | |

IE-SW-AL06LM-4TX-2SC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Accessories

www.weidmueller.com

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



General ordering data

| | | | |
|------------|----------------------------|---------------------------|--|
| Type | RM-KIT | Version | |
| Order No. | 1241440000 | Kit for 19"-rack mounting | |
| GTIN (EAN) | 4050118029154 | | |
| Qty. | 1 ST | | |