

**SAIL-M12BG-S3-7.0P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

Version	Power cable, One end without connector, M12, Number of poles : 3 (2 + PE), 7 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
Order No.	<a href="#">2706670700</a>
Type	SAIL-M12BG-S3-7.0P
GTIN (EAN)	4064675578192
Qty.	1 items

## SAIL-M12BG-S3-7.0P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E310075

## Dimensions and weights

Net weight 500 g

## Technical specifications for cable

Cable length	7 m	Sheathing colour	black
Resistance to oils	Yes	PE function	Yes
Suitable for cable carriers	Yes	Core cross-section	1.5 mm <sup>2</sup>
Shielded	No	Halogen	No
Insulation	PP	Acceleration	5 m/s <sup>2</sup>
Bending radius, min., moving	7.5 x cable diameter	Bending radius, min., stationary	4 x cable diameter
Bending cycles	10 Mio	Speed	5 m/s
Sheath material	PUR	Configurable cable length	No
LABS-free	Yes	Hydrolysis and microbe resistant	Yes
Outer cladding in accordance with UL AWM style	20234 (80 °C / 1000 V)	Irradiation crosslinked	No
Welding spark resistance	Yes	Colour coding	blue, brown, Green/yellow
Torsion resistance	270 °/m	Temperature range, stationary	-40...90 °C
Resistant to welding beads	Yes	Temperature range, moving	-40...90 °C
Number of poles	3 (2 + PE)	Outside diameter	8.5 mm ± 0.3 mm

## General technical data

Coding	S-coded	Connection thread	M12
Contact surface	Gold-plated	LED	No
Version	Female socket, straight	Housing main material	PUR
Insulation resistance	108 Ω	Nominal voltage	600 V
Nominal current	12 A	AF size	13 mm
Protection degree	IP67, when screwed in	Plugging cycles	≥ 100
Pollution severity	3	Temperature range of housing	-40 ... +85 °C
Tightening torque	M12: 1.0 Nm		

## Electrical properties

Insulation resistance 108 Ω Nominal voltage 600 V

## General standards

Certificate no. (cULus) E310075

## Plug, left

Plug left M12, S-coded, Number of poles: 3, female contact, straight, plug, unshielded

**SAIL-M12BG-S3-7.0P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Plug, right**

Plug right	Free conductor end
------------	--------------------

**Classifications**

ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-11
ECLASS 15.0	27-06-03-11		

**Drawings**

**Dimensioned drawing**



**Pole scheme**



**Wiring diagram**



**The ideal tool: Screwty® with torque function**

