


WTTB 6 PE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In T&D applications, current and voltage transformers are mainly used for protection and measurement functions. Our TTB range of Klippon® Connect instrument transformer terminal blocks have been designed to meet all the connection requirements of these two critical applications. The wiring of current and voltage transformers can be carried out particularly easily and safely with the new terminal block series – even within complex circuits. The prevention of operating errors during operation increases plant availability and extends the life cycle of the entire control cabinet. Thus, the respective requirements of the end user are fulfilled to the highest degree.

General ordering data

| | |
|------------|--|
| Version | PE terminal, Screw connection, Green/yellow, 6 mm ² , 500 V, Number of connections: 2, Number of levels: 1, TS 35, V-0, Wemid |
| Order No. | 2710100000 |
| Type | WTTB 6 PE |
| GTIN (EAN) | 4064675021124 |
| Qty. | 50 items |

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Depth | 69 mm | Depth (inches) | 2.7165 inch |
| Height | 100 mm | Height (inches) | 3.937 inch |
| Width | 8.1 mm | Width (inches) | 0.3189 inch |
| Net weight | 31.3 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -60 °C...85 °C |
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-------|--------|--------------|
| Basic material | Wemid | Colour | Green/yellow |
| UL 94 flammability rating | V-0 | | |

System specifications

| | | | |
|-------------------------------|-----|-------------------------------------|-------|
| End cover plate required | Yes | Number of potentials | 1 |
| Number of levels | 1 | Number of clamping points per level | 2 |
| Number of potentials per tier | 1 | Mounting rail | TS 35 |
| PE function | Yes | PEN function | No |

Additional technical data

| | | | |
|------------------|---------|--------------------------|-----|
| Open sides | right | Snap-on | Yes |
| Type of fixing | Snap-on | Explosion-tested version | No |
| Type of mounting | Snap-on | | |

CSA rating data

| | | | |
|-------------------------------|--------|-----------------------|-----------------|
| Wire cross section max. (CSA) | 8 AWG | Certificate No. (CSA) | 200039-80086745 |
| Wire cross section min. (CSA) | 22 AWG | | |

Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Conductors for clamping (rated connection)

| | | | |
|---|---------------------|---|---------------------|
| Gauge to IEC 60947-1 | A4 | Wire connection cross section AWG, max. | AWG 8 |
| Connection direction | on side | Tightening torque, max. | 1.6 Nm |
| Tightening torque, min. | 0.8 Nm | Stripping length | 12 mm |
| Type of connection | Screw connection | Number of connections | 2 |
| Clamping range, max. | 10 mm ² | Clamping range, min. | 0.5 mm ² |
| Clamping screw | M 3.5 | Blade size | 0.8 x 4.0 mm |
| Wire connection cross section AWG, min. | AWG 22 | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 6 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | Wire connection cross section, finely stranded, max. | 10 mm ² |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | Connection cross-section, stranded, max. | 6 mm ² |
| Connection cross-section, stranded, min. | 0.5 mm ² | Wire connection cross-section, solid core, max. | 10 mm ² |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | Connection cross-section, finely stranded, min. | 0.5 mm ² |

General

| | | | |
|---|---------------|---|--------|
| Wire connection cross section AWG, max. | AWG 8 | Wire connection cross section AWG, min. | AWG 22 |
| Standards | IEC 60947-7-2 | Mounting rail | TS 35 |

Rating data

| | | | |
|---|-------------------|--|---------|
| Rated cross-section | 6 mm ² | Rated voltage | 500 V |
| Rated voltage to adjoining terminal | 500 V | Rated DC voltage | 500 V |
| Standards | IEC 60947-7-2 | Volume resistance according to IEC 60947-7-x | 0.78 mΩ |
| Rated impulse withstand voltage | 6 kV | Rated impulse withstand voltage to adjacent terminal | 6 kV |
| Power loss in accordance with IEC 60947-7-x | 1.31 W | Surge voltage category | III |
| Pollution severity | 3 | | |



UL rating data

| | | | |
|--|--------|--|--------|
| Conductor size Factory wiring max. (cURus) | 8 AWG | Certificate No. (cURus) | E60693 |
| Conductor size Field wiring min. (cURus) | 22 AWG | Conductor size Factory wiring min. (cURus) | 22 AWG |
| Conductor size Field wiring max. (cURus) | 8 AWG | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000901 | ETIM 9.0 | EC000901 |
| ETIM 10.0 | EC000901 | ECLASS 14.0 | 27-25-01-03 |
| ECLASS 15.0 | 27-25-01-03 | | |

Drawings



WTTB 6 PE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Accessories

www.weidmueller.com

Accessorie



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | TS TTB 6 BK | Version |
| Order No. | 2710520000 | Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4050118881080 | |
| Qty. | 48 ST | |
| Type | TS TTB 6 BL | Version |
| Order No. | 2710480000 | Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4050118880656 | |
| Qty. | 48 ST | |
| Type | TS TTB 6 BR | Version |
| Order No. | 2715540000 | Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4050118769609 | |
| Qty. | 48 ST | |
| Type | TS TTB 6 GN | Version |
| Order No. | 2710490000 | Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4050118880953 | |
| Qty. | 48 ST | |
| Type | TS TTB 6 OR | Version |
| Order No. | 2710470000 | Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4050118880649 | |
| Qty. | 48 ST | |
| Type | TS TTB 6 RD | Version |
| Order No. | 2710510000 | Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4050118881073 | |
| Qty. | 48 ST | |
| Type | TS TTB 6 VT | Version |
| Order No. | 2710530000 | Socket (terminal), Plug-in depth: 11.5 mm, 0.00 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4050118881097 | |
| Qty. | 48 ST | |
| Type | TS TTB 6 WT | Version |
| Order No. | 2817250000 | Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4064675322566 | |
| Qty. | 48 ST | |
| Type | TS TTB 6 YL | Version |
| Order No. | 2710500000 | Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm |
| GTIN (EAN) | 4050118881066 | |
| Qty. | 48 ST | |
| Type | SL TTB 6 | Version |
| Order No. | 2710220000 | Lockout device (terminal), PA 66/6, red |
| GTIN (EAN) | 4050118893311 | |
| Qty. | 50 ST | |

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--------------------------|
| Type | LL TTB 6/1 | Version |
| Order No. | 2710230000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118847925 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/1 BK | Version |
| Order No. | 2710280000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118847963 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/1 BL | Version |
| Order No. | 2710240000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118847918 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/1 BR | Version |
| Order No. | 2762590000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675018377 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/1 GN | Version |
| Order No. | 2710250000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118847949 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/1 RD | Version |
| Order No. | 2710270000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118847956 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/1 VT | Version |
| Order No. | 2710290000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118847970 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/1 WT | Version |
| Order No. | 2817220000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675322535 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/1 YL | Version |
| Order No. | 2710260000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118893335 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 | Version |
| Order No. | 2710300000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848243 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 BK | Version |
| Order No. | 2710350000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848274 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 BL | Version |
| Order No. | 2710310000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848250 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 BR | Version |
| Order No. | 2762600000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675018384 | |
| Qty. | 50 ST | |

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--------------------------|
| Type | LL TTB 6/2 CM | Version |
| Order No. | 2710370000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012092 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 CM BK | Version |
| Order No. | 2710420000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012641 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 CM BL | Version |
| Order No. | 2710380000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012603 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 CM BR | Version |
| Order No. | 2762610000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675018391 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 CM GN | Version |
| Order No. | 2710390000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012610 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 CM RD | Version |
| Order No. | 2710410000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012634 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 CM VT | Version |
| Order No. | 2710430000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012658 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 CM WT | Version |
| Order No. | 2817240000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675322559 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 CM YL | Version |
| Order No. | 2710400000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012627 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 GN | Version |
| Order No. | 2710320000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848328 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 RD | Version |
| Order No. | 2710340000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848281 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 VT | Version |
| Order No. | 2710360000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848267 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/2 WT | Version |
| Order No. | 2817230000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675322542 | |
| Qty. | 50 ST | |

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

| | | |
|------------|----------------------------|--------------------------|
| Type | LL TTB 6/2 YL | Version |
| Order No. | 2710330000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848311 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/3 | Version |
| Order No. | 2710440000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848236 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/3 CM | Version |
| Order No. | 2726100000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012665 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/4 | Version |
| Order No. | 2710450000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848229 | |
| Qty. | 25 ST | |
| Type | LL TTB 6/4 CM | Version |
| Order No. | 2726110000 | Locking lever (terminal) |
| GTIN (EAN) | 4064675012672 | |
| Qty. | 50 ST | |
| Type | LL TTB 6/6 | Version |
| Order No. | 2710460000 | Locking lever (terminal) |
| GTIN (EAN) | 4050118848212 | |
| Qty. | 10 ST | |

End plates and partition plates



Partition plates and end plates are essential accessories for terminal blocks. Partition plates provide optical and electrical separation of different potentials and functional groups, increasing safety and ensuring a clear structure inside the control cabinet. End plates close the terminal block row on the sides, protect against contact with live parts, and ensure a clean, stable finish. Both components are precisely matched to the respective Weidmüller terminal block series, contributing to safe, compliant, and professional wiring.

General ordering data

| | | |
|------------|----------------------------|---------------------|
| Type | EP TTB 6 | Version |
| Order No. | 2710170000 | A-series, End plate |
| GTIN (EAN) | 4050118822229 | |
| Qty. | 20 ST | |

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

| | | |
|------------|----------------------------|-----------------------|
| Type | AEB 35 SCL/1 V0 | Version |
| Order No. | 2661280000 | A-series, End bracket |
| GTIN (EAN) | 4050118702163 | |
| Qty. | 20 ST | |
| Type | AEB 35 SCL/1 V0 BK | Version |
| Order No. | 2661300000 | A-series, End bracket |
| GTIN (EAN) | 4050118702187 | |
| Qty. | 20 ST | |
| Type | AEB 35 SCL/1 V0 GY | Version |
| Order No. | 2661290000 | A-series, End bracket |
| GTIN (EAN) | 4050118702170 | |
| Qty. | 20 ST | |

Accessorie



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SCCB TT6 6/2 | Version |
| Order No. | 2710190000 | Cross-connector (terminal), Plugged, orange, 30 A, Number of poles: |
| GTIN (EAN) | 4050118847987 | 2, Pitch in mm (P): 8.10, Insulated: Yes, Width: 16 mm |
| Qty. | 25 ST | |
| Type | SCCB TT6 6/3 | Version |
| Order No. | 2710200000 | Cross-connector (terminal), Plugged, orange, 30 A, Number of poles: |
| GTIN (EAN) | 4050118847994 | 3, Pitch in mm (P): 8.10, Insulated: Yes, Width: 24.1 mm |
| Qty. | 25 ST | |
| Type | SCCB TT6 6/4 | Version |
| Order No. | 2710210000 | Cross-connector (terminal), Plugged, orange, 30 A, Number of poles: |
| GTIN (EAN) | 4050118848007 | 4, Pitch in mm (P): 8.10, Insulated: Yes, Width: 32.2 mm |
| Qty. | 25 ST | |

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | ZQV 6N/10 | Version |
| Order No. | 2733970000 | Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: |
| GTIN (EAN) | 4064675066811 | 10, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm |
| Qty. | 20 ST | |
| Type | ZQV 6N/6 | Version |
| Order No. | 2733950000 | Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: |
| GTIN (EAN) | 4064675066699 | 6, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm |
| Qty. | 20 ST | |
| Type | ZQV 6N/7 | Version |
| Order No. | 2733960000 | Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: |
| GTIN (EAN) | 4064675066804 | 7, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm |
| Qty. | 20 ST | |

Accessorie



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

General ordering data

| | | |
|------------|----------------------------|-----------------------|
| Type | CH TTB | Version |
| Order No. | 2710130000 | Cover hood (terminal) |
| GTIN (EAN) | 4064675021155 | |
| Qty. | 1 ST | |
| Type | CP TTB | Version |
| Order No. | 2710140000 | Cover hood (terminal) |
| GTIN (EAN) | 4064675014171 | |
| Qty. | 10 ST | |
| Type | CS TTB | Version |
| Order No. | 2710150000 | A-series, End bracket |
| GTIN (EAN) | 4064675021148 | |
| Qty. | 10 ST | |

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

Accessories

www.weidmueller.com

DEK 5/8



WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

General ordering data

| | | | |
|------------|----------------------------|--|--|
| Type | DEK-A 5/8 MM WS | Version | |
| Order No. | 2448860000 | Dekafix, Terminal marker, 5 x 8.1 mm, Weidmueller, white | |
| GTIN (EAN) | 4050118462968 | | |
| Qty. | 500 ST | | |

Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
 - Strips for fast installation
 - Terminal markers, suitable for all Weidmüller cable connectors
 - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | | | |
|------------|----------------------------|---|--|
| Type | DEK 5/8-11.5 MC NE WS | Version | |
| Order No. | 1341630000 | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 | |
| GTIN (EAN) | 4050118145946 | Weidmueller, white | |
| Qty. | 500 ST | | |

WTTB 6 PE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany

Accessories

www.weidmueller.com

Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | ZQV 6N/10 BL | Version |
| Order No. | 2786910000 | Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 10, |
| GTIN (EAN) | 4064675064602 | Pitch in mm (P): 8.00, Insulated: Yes, Width: 78.7 mm |
| Qty. | 20 ST | |
| Type | ZQV 6N/2 | Version |
| Order No. | 1985740000 | Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: |
| GTIN (EAN) | 4050118370362 | 2, Pitch in mm (P): 8.00, Insulated: Yes, Width: 13.7 mm |
| Qty. | 60 ST | |
| Type | ZQV 6N/3 | Version |
| Order No. | 1985760000 | Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: |
| GTIN (EAN) | 4050118370263 | 3, Pitch in mm (P): 8.00, Insulated: Yes, Width: 21.8 mm |
| Qty. | 60 ST | |
| Type | ZQV 6N/3 BL | Version |
| Order No. | 1985840000 | Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 3, |
| GTIN (EAN) | 4050118370379 | Pitch in mm (P): 8.00, Insulated: Yes, Width: 21.8 mm |
| Qty. | 60 ST | |
| Type | ZQV 6N/4 | Version |
| Order No. | 1985780000 | Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: |
| GTIN (EAN) | 4050118370287 | 4, Pitch in mm (P): 8.00, Insulated: Yes, Width: 29.9 mm |
| Qty. | 60 ST | |
| Type | ZQV 6N/4 BL | Version |
| Order No. | 1985850000 | Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 4, |
| GTIN (EAN) | 4050118370447 | Pitch in mm (P): 8.00, Insulated: Yes, Width: 29.9 mm |
| Qty. | 60 ST | |
| Type | ZQV 6N/6 BL | Version |
| Order No. | 2786890000 | Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 6, |
| GTIN (EAN) | 4064675064572 | Pitch in mm (P): 8.00, Insulated: Yes, Width: 46.3 mm |
| Qty. | 20 ST | |
| Type | ZQV 6N/7 BL | Version |
| Order No. | 2786900000 | Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 7, |
| GTIN (EAN) | 4064675064596 | Pitch in mm (P): 8.00, Insulated: Yes, Width: 54.4 mm |
| Qty. | 20 ST | |