

**THM WO-Q 25/19.1 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 2 - 3.8 mm, 25 x 19.1 mm, white
Order No.	<a href="#">2711870000</a>
Type	THM WO-Q 25/19.1 WS
GTIN (EAN)	4050118750065
Qty.	1000 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	0.03 mm	Depth (inches)	0.0012 inch
Height	25 mm	Height (inches)	0.9842 inch
Width	19.1 mm	Width (inches)	0.752 inch
Net weight	0.08 g		

**Temperatures**

Operating temperature range	-40...150 °C
-----------------------------	--------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General data**

Adhesive	Polyacrylate adhesive		
Orientation of print	horizontal and vertical		
Type of printing	neutral		
Width	19.1 mm		
UL 94 flammability rating	V-0		
Operating temperature range, max.	150 °C		
Operating temperature range, min.	-40 °C		
Colour	white		
Halogen	No		
Basic material	Polyester film		
Printed characters	without		
Number of markers per packaging unit	Form of supply	Label reel	
Size of labelling field	25 x 9 mm		
Approval acc. to UL 969	Yes		
compatible printer	<a href="#">THM MULTIMARK</a> , <a href="#">THM MULTIMARK PLUS</a>		
Number of markers per combination	1 Label reel = Conductor and cable markers		
Operating temperature range	-40...150 °C		
Number per roll	1000		

**Conductor and cable markers**

Halogen	No	Conductor cross-section, max.	11 mm <sup>2</sup>
Conductor O.D., max.	3.8 mm	Conductor O.D., min.	2 mm
Conductor O.D.	2 - 3.8 mm	Cross-section for connected wire	11 mm <sup>2</sup>

**Classifications**

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		

**Drawings**



## THM WO-Q 25/19.1 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Accessories

[www.weidmueller.com](http://www.weidmueller.com)

### Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

Type	RIBBON MM 76/360 SW	Version	
Order No.	<a href="#">2005080000</a>	Ink ribbon	
GTIN (EAN)	4050118389951		
Qty.	1 ST		
Type	RIBBON MM 110/360 SW	Version	
Order No.	<a href="#">2005070000</a>	Ink ribbon	
GTIN (EAN)	4050118390049		
Qty.	1 ST		