Data sheet

SAISGS-P-5K-8/13-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

General ordering data

Version	Field attachable connector, M12
Order No.	2703490000
Type	SAISGS-P-5K-8/13-M12
GTIN (EAN)	4050118773064
Qty.	1 items

Data sheet

SAISGS-P-5K-8/13-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform

Dimensions and weights

Net weight	42.38 g

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1
SCIP	ebf89fc8-a87f-4691-b87a-dfb9921774b4

Technical data customisable plug-in connectors

Number of poles	5	Coding	K-coded
Contact surface	Au (Gold)	Type of connection	Screw connection
Housing main material	PA	Cable diameter, max.	13 mm
Cable diameter, min.	8 mm	Contact material	CuZn
Nominal voltage	630 V	Nominal current	12 A
Protection degree	IP67	Plugging cycles	≥ 100
Pollution severity	3	Gender of contact	Male
Shield connection	No	Threaded ring material	Diecast zinc
Temperature range of housing	-40 ... +85 ° C	Connection cross-section, max.	2.5 mm²

General Info

Number of poles	5	Connection 1	M12
Connection 2	Screw	Housing main material	PA
Connection thread	M12	Contact material	CuZn
Contact surface	Au (Gold)	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	1.5 mm²
Protection degree	IP67	Plugging cycles	≥ 100

Classifications

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		

SAISGS-P-5K-8/13-M12

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



