

PNP-63-MOD-TCP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Plug&Play Boxes**

With the ready-to-connect Plug&Play boxes, existing machines can be easily integrated into the IoT network, without costly intervention in the control cabinet structures.

The boxes thus serve as data collectors and are at the same time the basis for the evaluation and transparent display of your energy consumption.

All you need is a network connection near the Plug&Play boxes.

General ordering data

Order No.	2716670000
Type	PNP-63-MOD-TCP
GTIN (EAN)	4064675002550
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2025-04-08T00:00:00+02:00

PNP-63-MOD-TCP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	225 mm	Depth (inches)	8.8582 inch
Height	340 mm	Height (inches)	13.3858 inch
Width	540 mm	Width (inches)	21.2598 inch
Net weight	999 g		

Temperatures

Storage temperature	-25 °C...70 °C	Humidity at storage temperature	0...90 % (no condensation)
Ambient temperature	-10 °C...40 °C	Operating temperature	
Humidity	0...75 % RH (at ambient temperature)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6aI, 6c, 7a, 7cI
REACH SVHC	Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1, Lead monoxide 1317-36-8
SCIP	b8594349-3937-4fc3-b3f9-0b9575c3ba7d

Measuring current input

Rated current	63 A
---------------	------

Communication

Interface	Ethernet 10/100 Base-TX (RJ-45 socket), Web server/e-mail	Protocol	TCP/IP, DHCP Client (BootP), Modbus/TCP (Port 502), ICMP (Ping), NTP, Modbus RTU over Ethernet (Port 8000), FTP, SNMP
-----------	---	----------	---

Inputs/outputs

Number of digital inputs	0	Temperature input	Yes
--------------------------	---	-------------------	-----

Technical data

Applications	Power and flow measurement	Type of mounting	Wall mounting; Connection side lying, DIN rail
Protection degree	IP54, IP20	Pollution severity	4
Rated current	63 A	Air pressure (operation)	≥ 795 hPa (height ≤ 2000 m) as per DIN EN 61131-2
Usage	Plug & Play	Display monitoring (monitor)	LCD
Standards	IEC 61439-2	Measurement range, voltage L-L, AC	480 V
Surge voltage category	II	Supply voltage	via the input measuring circuit
Sampling frequency 50/60 Hz	40 kHz		

Insulation coordination

Surge voltage category	II	Pollution severity	4
------------------------	----	--------------------	---

PNP-63-MOD-TCP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Important note

Product information	<p>Flow measurement The PNP-63-MOD-TCP and PNP-U-MOD-TCP products work with an external flow sensor. The signal line of the sensor is connected to the measuring device via an SAI connection.</p> <p>Temperature measurement The ambient temperature is recorded with an external temperature sensor. The signal line of the sensor is connected to the measuring device via an SAI connection.</p> <p>Power consumption measurement The PNP-16-MOD-TCP, PNP-32-MOD-TCP and PNP-63-MOD-TCP products are provided with integrated current transformers. The power line is guided via the CEE connections through the measuring device to the machine or plant. The PNP-U-MOD-TCP product works with external current transformers. The signal lines of the current transformers are connected to the measuring device via HDC connections.</p> <p>Communication The measured values are transferred from the measuring device to the network via a data line. The measured values can be displayed in real time on a connected PC.</p>
---------------------	--

Classifications

ETIM 8.0	EC002301	ETIM 9.0	EC002301
ETIM 10.0	EC002301	ECLASS 14.0	27-14-23-30
ECLASS 15.0	27-14-23-30		

Drawings

