

**HDC 06B AF WM COVER****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

Our flange-mounted housings made of plastic have a built-in cable gland and a screw interlock. They seal directly onto the panel wall and can therefore be used without an attachment housing. The housings are impressive with their low weight and optimal protection against contamination, water and vibrations.

**General ordering data**

Version	HDC enclosures, Installation size: 3, Protection degree: IP66, in plugged condition, Cover for lower part of housing, Screw
Order No.	<a href="#">2716810000</a>
Type	HDC 06B AF WM COVER
GTIN (EAN)	4050118803686
Qty.	1 items

## HDC 06B AF WM COVER

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

## Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E223801

## Dimensions and weights

Depth	55 mm	Depth (inches)	2.1654 inch
Height	39.5 mm	Height (inches)	1.5551 inch
Width	100.5 mm	Width (inches)	3.9567 inch
Length	100.5 mm	Length (inches)	3.9567 inch
Net weight	4.6 g		

## Temperatures

Ambient temperature	-20 °C...100 °C
---------------------	-----------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Dimensions

Cable entry	No
-------------	----

## General data

Tightening torque	3 Nm	UL 94 flammability rating	V-0
Housing main material	PA	Protection degree	IP66, in plugged condition
EMC housings	No	Material of locking element	Stainless steel, rust-proof

## Version

Top part/bottom part/lid	Cover	Cover	with cover
Tightening torque	3 Nm	Number of cable entry sideways	0
Design of housing	Cover for lower part of housing	Design of locking system	Screw
Installation size	3	Cable entry	No
Type	Cover	Sealing	NBR
Colour (RAL)	RAL 7035	BG	3
Suitable for ModuPlug®	Yes		

## Classifications

ETIM 8.0	EC000437	ETIM 9.0	EC000437
ETIM 10.0	EC000437	ECLASS 14.0	27-44-02-02
ECLASS 15.0	27-44-02-02		