


SFM 4/18 3.3-4.0 MM GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



With the comprehensive MultiMark product family, you can achieve optimally structured and sustainable marking in every control cabinet. An example of this is our new SlimFix wire marker, which can be printed and snapped on particularly quickly. At the same time, they meet the highest requirements for vibration and shock resistance. The wire markers have an open design and can be easily and quickly installed before or after the wiring process.

General ordering data

| | |
|------------|--|
| Version | Conductor and cable markers, 2.5 - 4 mm, 18 x 5.7 mm, yellow |
| Order No. | 2719250000 |
| Type | SFM 4/18 3.3-4.0 MM GE |
| GTIN (EAN) | 4050118888287 |
| Qty. | 800 items |

SFM 4/18 3.3-4.0 MM GE

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 18 mm | Height (inches) | 0.7087 inch |
| Width | 5.7 mm | Width (inches) | 0.2244 inch |
| Net weight | 0.3 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|-------------------------|-----------------------------------|---------------|
| Orientation of print | horizontal and vertical | Type of printing | neutral |
| Version | with snap-in foot | Width | 5.7 mm |
| UL 94 flammability rating | V-2 | Operating temperature range, max. | 90 °C |
| Operating temperature range, min. | -50 °C | Colour | yellow |
| Halogen | No | Basic material | PC-ABS, TPU |
| Printed characters | without | Size of labelling field | 4.9 x 15.5 mm |
| Number per roll | 800 | | |

Conductor and cable markers

| | | | |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen | No | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 3.3 mm ² | Conductor O.D., max. | 4 mm |
| Conductor O.D., min. | 2.5 mm | Conductor O.D. | 2.5 - 4 mm |
| Cross-section for connected wire | 3.3 - 4 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

SFM 4/18 3.3-4.0 MM GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings




SFM 4/18 3.3-4.0 MM GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|---------|--|
| Type | MULTIMARK ROLLER SFM 4 | Version | |
| Order No. | 2835010000 | | |
| GTIN (EAN) | 4064675427346 | | |
| Qty. | 1 ST | | |

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | | |
|------------|----------------------------|------------|--|
| Type | RIBBON MM-TB 25/360 SW | Version | |
| Order No. | 2005090000 | Ink ribbon | |
| GTIN (EAN) | 4050118390216 | | |
| Qty. | 1 ST | | |