

TS 35X7.5/1.0 2M/CU/BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Copper has the best electrical conductivity of all metals used. The copper rail has the highest short-circuit protection.

General ordering data

Version	Terminal rail, Accessories, Copper, untreated, Width: 2000 mm, Height: 35 mm, Depth: 7.5 mm
Order No.	2731380000
Type	TS 35X7.5/1.0 2M/CU/BK
GTIN (EAN)	4050118810882
Qty.	40 M

TS 35X7.5/1.0 2M/CU/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.2953 inch
Height	35 mm	Height (inches)	1.378 inch
Width	2000 mm	Width (inches)	78.74 inch
Net weight	352.41 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Mounting rail

Standards	DIN EN 60715	
Surface finish	untreated	
Thickness	1.00 mm	
Basic material	Copper	
Length of the terminal rail	min.	0 mm
	nominal	2000 mm
	max.	2000 mm
Permitted thermal current for PEN function, max.	150.00 A	
Short-time withstand current per second 6 kA according to IEC 60947-7-2		
Pre-punched mounting rail	No	
Slit width		
Short circuit strength corresponds to E-Cu wire	50.00 mm²	
Spacing of holes, centre-to-centre	0 mm	
Slit gap		
Slit length		

Classifications

ETIM 8.0	EC001285	ETIM 9.0	EC001285
ETIM 10.0	EC001285	ECLASS 14.0	27-40-06-02
ECLASS 15.0	27-40-06-02		

TS 35X7.5/1.0 2M/CU/BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

