

**SAIL-M12BG-S3-9.OP****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

Your peripheral devices should be supplied with greater power. With our new M12 plug-in connector, more than 250 V and 2 A is possible without problems. The compact A-, K-, L-, S- and T-coded M12 plug-in connectors are designed for the transmission of up to 630 V AC or 60 V DC and 12 A.

**General ordering data**

Version	Power cable, One end without connector, M12, Number of poles : 3 (2 + PE), 9 m, Female socket, straight, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
Order No.	<a href="#">2706670900</a>
Type	SAIL-M12BG-S3-9.OP
GTIN (EAN)	4064675578208
Qty.	1 items

## SAIL-M12BG-S3-9.0P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E310075

## Dimensions and weights

Net weight 700 g

## Technical specifications for cable

Cable length	9 m	Sheathing colour	black
Resistance to oils	EN 50363-10-2	PE function	Yes
Suitable for cable carriers	Yes	Core cross-section	1.5 mm <sup>2</sup>
Number of wires	3	Shielded	No
Halogen	No	Insulation	PP
Acceleration	5 m/s <sup>2</sup>	Bending radius, min., moving	7.5 x cable diameter
Bending radius, min., stationary	4 x cable diameter	Bending cycles	10 Mio
Resistance to spread of flame	in accordance with IEC 60332-1-2	Speed	300 m/min
Sheath material	PUR	Cable length configurable	No
LABS-free	Yes	Hydrolysis and microbe resistant	Yes
Outer cladding in accordance with UL AWM style	20234 (80 °C / 1000 V)	Hybrid cable	No
Irradiation crosslinked	No	Welding spark resistance	Yes
Colour coding	brown, Green/yellow, blue	Torsion resistance	270 °/m
Temperature range, stationary	-40...80 °C	Resistant to welding beads	Yes
Temperature range, moving	-25...60 °C	Number of poles	3 (2 + PE)

## General technical data

Coding	S-coded	Connection thread	M12
Contact surface	Gold-plated	LED	No
Version	Female socket, straight	Housing main material	PUR
Insulation resistance	108 Ω	Contact material	Copper alloy
Nominal voltage	600 V	Nominal current	12 A
AF size	13 mm	Protection degree	IP65, IP67, when screwed in
Plugging cycles	≥ 100	Pollution severity	3
Threaded ring material	Brass, nickel-plated	Temperature range of housing	-40 ... +85 °C
Tightening torque	M12: 1.0 Nm		

## Electrical properties

Insulation resistance 108 Ω Nominal voltage 600 V

## General standards

Connector standard IEC 61076-2-101 Certificate no. (cULus) E310075

**SAIL-M12BG-S3-9.0P**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

**Standards**

Connector standard	IEC 61076-2-101
--------------------	-----------------

**Plug, left**

Plug left	M12, S-coded, Number of poles: 3, female contact, straight, plug, unshielded
-----------	--

**Plug, right**

Plug right	Free conductor end
------------	--------------------

**Classifications**

ETIM 8.0	EC001855	ETIM 9.0	EC001855
ETIM 10.0	EC001855	ECLASS 14.0	27-06-03-11
ECLASS 15.0	27-06-03-11		

Drawings

Dimensioned drawing



Pole scheme



Wiring diagram



The ideal tool: Screwty® with torque function

