

SCCB TTB 6/2**Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

General ordering data

| | |
|------------|--|
| Version | Cross-connector (terminal), Plugged, orange, 30 A, Number of poles: 2, Pitch in mm (P): 8.10, Insulated: Yes, Width: 16 mm |
| Order No. | 2710190000 |
| Type | SCCB TTB 6/2 |
| GTIN (EAN) | 4050118847987 |
| Qty. | 25 items |

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 13.47 mm | Depth (inches) | 0.5303 inch |
| Height | 14.06 mm | Height (inches) | 0.5535 inch |
| Width | 16 mm | Width (inches) | 0.6299 inch |
| Net weight | 2.75 g | | |

Temperatures

| | |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|---------------------------|-------|--------|--------|
| Basic material | Wemid | Colour | orange |
| UL 94 flammability rating | V-0 | | |

System specifications

| | |
|---------|-----------------|
| Version | Cross-connector |
|---------|-----------------|

Additional technical data

| | | | |
|------------------|---------|--------------------------|----|
| Type of fixing | Plugged | Explosion-tested version | No |
| Type of mounting | Plugged | | |

Dimensions

| | |
|-----------------|---------|
| Pitch in mm (P) | 8.10 mm |
|-----------------|---------|

General

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Rating data

| | | | |
|---------------|-------|-----------------|------|
| Rated voltage | 500 V | Nominal current | 30 A |
|---------------|-------|-----------------|------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |

Drawings

