

USB2.0B T1V 3.0N4 TY BK
Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



USB as a reliable data interface for your device in industrial use. Due to the many advantages, USB sockets are always used most in the electrical industry.

The extensive portfolio of USB-A, -B - C and -Micro components enables future-proof device design with speeds of up to 10 Gbit/s. Our USB PCB sockets support the robust standards USB 2.0, 3.0 and 3.1 for fast and easy data transfer.

The individual connectors meet the requirements for high durability and offer reliable connectivity.

- Up to 10.000 plugging cycles
- THT, THR or SMD soldering processes
- Available in design types 180° (vertical/upright) or 90° (horizontal/flat-lying)
- Packed either in a tray (TY) or on a roll (tape-on-reel, RL)
- Reinforced gold layer for improved corrosion protection
- USB 3.1 sockets support data rates of 10 Gbit/s for fast data transfer
- USB-C sockets enable error-free plugging due to a symmetrical design
- Robust plug & play operation - connect and disconnect without shutting down or restarting the system

General ordering data

Version	OMNIMATE Data - USB jack, PCB plug-in connector, USB 3.0, Type B, 480 Mbps, THT solder connection, 180°, Plugging cycles: ≥ 1500, Number of poles: 4, PBT, Gold over nickel, Tray (manual assembly)
Order No.	2710810000
Type	USB2.0B T1V 3.0N4 TY BK
GTIN (EAN)	4050118757866
Qty.	110 items
Packaging	Tray (manual assembly)
Delivery status	Discontinued
Last order date	2025-11-01T00:00:00+01:00

USB2.0B T1V 3.0N4 TY BK

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	11.2 mm	Depth (inches)	0.4409 inch
Height	16.1 mm	Height (inches)	0.6339 inch
Width	12.2 mm	Width (inches)	0.4803 inch
Net weight	3.76 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

System specifications

Number of poles	4	LED	No
Solder pin length (l)	3.05 mm	Mounting onto the PCB	THT solder connection
Pitch in inches (P)	0.098 "	Shielding material	Brass
Shielding	Yes	Side termination, characteristic	Solder flange
Transmission rate	480 Mbps	Type of connection	Solder connection
Product family	OMNIMATE Data - USB jack	Pitch in mm (P)	2.50 mm
Protection degree	IP20	Plugging cycles	≥ 1500
Outgoing elbow	180°	Shield surface	nickel-plated
Shield tabs	none	Performance-Category	480 Mbps
Soldering process	Manual soldering, Wave soldering	Solder pin dimensions	Octagonal
Tolerance of solder pin position	± 0.1 mm		

Electrical properties

Dielectric strength, contact / contact	500 V AC	Insulation resistance	≥ 1000 MΩ
Nominal voltage	30 V		

Material data

Insulating material	PBT	Colour	black
Colour chart (similar)	RAL 9011	Insulation resistance	≥ 1000 MΩ
Moisture Level (MSL)		UL 94 flammability rating	V-0
Contact base material	Copper alloy	Contact material	Cu-alloy
Contact surface	Gold over nickel	Layer structure of plug contact	30 μ" Au
Storage temperature, min.	-40 °C	Storage temperature, max.	70 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C

Packing

Packaging	Tray (manual assembly)	VPE length	310.00 mm
VPE width	230.00 mm	VPE height	14.00 mm

Important note

Notes

USB2.0B T1V 3.0N4 TY BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		

USB2.0B T1V 3.0N4 TY BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings




USB2.0B T1V 3.0N4 TY BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



USB2.0B T1V 3.0N4 TY BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Legend

USB	3.0A	R	1	V	3.0	N	4	TY	BL	USB3.0A R1V 3.0N4 TY BL		
										Colour / Special Option	BL BK WH SO	blue (plastic) black (plastic) white (plastic) customized product
										Packaging	TY RL TU	Tray in box (manual assembly) Tape on Reel (automated assembly) Tube
										Contact surface thickness	4	1 = 3μ", 2 = 6μ", 3 = 15μ", 4 = 30μ", 5 = 50μ"
											N	no use
										Solder Pin length	3.2 1.6 D	3.2 mm 1.6 mm SMD
										Direction	H U V	Horizontal (90°, side entry) Horizontal, Upright 90° Vertical (180°, top entry)
										Number of Ports	1 21; 41; ...	1 Port multi ports about each other, Multilevel
										Assembly on PCB	R S T	Through Hole Reflow - THR Soldering process: Wave or Reflow soldering Surface Mount Technology - SMT Soldering process: Reflow soldering Through Hole Technology - THT Soldering process: Wave
										Type / Performance	2.0A 3.0A	USB 2.0 Type A USB 3.0 Type A