


SFM 4/12 3.3-4.0 MM WS**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com

With the comprehensive MultiMark product family, you can achieve optimally structured and sustainable marking in every control cabinet. An example of this is our new SlimFix wire marker, which can be printed and snapped on particularly quickly. At the same time, they meet the highest requirements for vibration and shock resistance. The wire markers have an open design and can be easily and quickly installed before or after the wiring process.

General ordering data

| | |
|------------|---|
| Version | Conductor and cable markers, 2.5 - 4 mm, 12 x 5.7 mm, white |
| Order No. | 2719210000 |
| Type | SFM 4/12 3.3-4.0 MM WS |
| GTIN (EAN) | 4050118888249 |
| Qty. | 1200 items |

SFM 4/12 3.3-4.0 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

| | |
|------|---------|
| RoHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 12 mm | Height (inches) | 0.4724 inch |
| Width | 5.7 mm | Width (inches) | 0.2244 inch |
| Net weight | 0.22 g | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

General data

| | | | |
|-----------------------------------|-------------------------|-----------------------------------|--------------|
| Orientation of print | horizontal and vertical | Type of printing | neutral |
| Version | with snap-in foot | Width | 5.7 mm |
| UL 94 flammability rating | V-2 | Operating temperature range, max. | 90 °C |
| Operating temperature range, min. | -50 °C | Colour | white |
| Halogen | No | Basic material | PC-ABS, TPU |
| Printed characters | without | Size of labelling field | 4.9 x 9.5 mm |
| Number per roll | 1200 | | |

Conductor and cable markers

| | | | |
|----------------------------------|-------------------------|-------------------------------|-------------------|
| Halogen | No | Conductor cross-section, max. | 4 mm ² |
| Conductor cross-section, min. | 3.3 mm ² | Conductor O.D., max. | 4 mm |
| Conductor O.D., min. | 2.5 mm | Conductor O.D. | 2.5 - 4 mm |
| Cross-section for connected wire | 3.3 - 4 mm ² | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ETIM 10.0 | EC001530 | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 | | |

SFM 4/12 3.3-4.0 MM WS

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

