


APG 1.5/8-7BG-GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

General ordering data

| | |
|------------|---|
| Version | Plug, 1.5 mm ² , 500 V, 17.5 A, Number of poles: 8, dark beige |
| Order No. | 2719810000 |
| Type | APG 1.5/8-7BG-GN |
| GTIN (EAN) | 4050118811179 |
| Qty. | 20 items |

APG 1.5/8-7BG-GN

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|----------|-----------------|-------------|
| Depth | 31.15 mm | Depth (inches) | 1.2264 inch |
| Height | 14 mm | Height (inches) | 0.5512 inch |
| Width | 28 mm | Width (inches) | 1.1024 inch |
| Net weight | 9.31 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|----------------|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -60 °C...85 °C |
| Continuous operating temp., min. | -60 °C | Continuous operating temp., max. | 130 °C |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|--------------------------------|--------|---------------------------|------------|
| Basic material | Wemid | Colour | dark beige |
| Colour of operational elements | orange | UL 94 flammability rating | V-0 |

System specifications

| | | | |
|--------------------------|----|----------------------|---|
| End cover plate required | No | Number of potentials | 8 |
| Number of levels | 1 | | |

Additional technical data

| | |
|------------------|---------|
| Type of mounting | Plugged |
|------------------|---------|

Conductors for clamping (rated connection)

| | | | |
|---|---------------------|---|----------------------|
| Gauge to IEC 60947-1 | A1 | Wire connection cross section AWG, max. | AWG 14 |
| Connection direction | top | Stripping length | 10 mm |
| Type of connection | PUSH IN | Number of connections | 8 |
| Clamping range, max. | 1.5 mm ² | Clamping range, min. | 0.14 mm ² |
| Blade size | 0.4 x 2.0 mm | Wire connection cross section AWG, min. | AWG 26 |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 1.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.14 mm ² |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 1.5 mm ² | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.14 mm ² |
| Wire connection cross section, finely stranded, max. | 1.5 mm ² | Wire connection cross section, finely stranded, min. | 0.14 mm ² |
| Connection cross-section, stranded, max. | 1.5 mm ² | Connection cross-section, stranded, min. | 0.14 mm ² |
| Wire connection cross-section, solid core, max. | 1.5 mm ² | Wire connection cross-section, solid core, min. | 0.14 mm ² |

APG 1.5/8-7BG-GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

General

| | | | |
|---|--------|---|----------------------------------|
| Number of poles | 8 | Wire connection cross section AWG, max. | AWG 14 |
| Wire connection cross section AWG, min. | AWG 26 | Standards | In accordance with IEC 60947-7-1 |

Rating data

| | | | |
|-------------------------------------|----------------------------------|--|---------|
| Rated cross-section | 1.5 mm ² | Rated voltage | 500 V |
| Rated voltage to adjoining terminal | 500 V | Rated DC voltage | 500 V |
| Nominal current | 17.5 A | Current at maximum wires | 17.5 A |
| Standards | In accordance with IEC 60947-7-1 | Volume resistance according to IEC 60947-7-x | 1.83 mΩ |
| Rated impulse withstand voltage | 6 kV | Power loss in accordance with IEC 60947-7-x | 0.56 W |
| Surge voltage category | III | Pollution severity | 3 |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002848 | ETIM 9.0 | EC002848 |
| ETIM 10.0 | EC002848 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 | | |