

## FMH1 S1/20V F1 B RL

Weidmüller Interface GmbH & Co. KG


Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

### Product image



#### OMNIMATE® - Board-to-Board connectors

##### Flexible engineering of compact devices

The use of future-proof contact systems, as well as the optimisation of manufacturing processes, are increasingly important in the development of efficient industrial devices, especially in the field of Industry 4.0. OMNIMATE® board-to-board connectors feature a 1.27 mm pitch and offer maximum flexibility due to different designs.

- Flexible device design - Industrial suitable density combined with high flexible connection combinations (Mezzanine, Mother-to-Daughter, Extender-card, Cable-to-Board)
- Automation-Ready - Developed for automatic assembly with high precise pin coplanarity and SMT-fixation
- Reliable contact - Up to 500 mating cycles due to industrial suitable gold-surface (PdNi-Au)
- Process-Ready - High performance LCP material for reflow soldering
- Scalability - Different heights with high contact overlapping ensure various solutions from 12 – 80 poles.
- Robust miniaturisation - simple and safe connection even possible under unfavorable mating conditions – e.g. inclination or offset.

#### General ordering data

Version	PCB plug-in connector, male header, SMD solder connection, Pitch in mm (P): 1.27 mm, Number of poles: 20, 180°, Tape
Order No.	<a href="#">2747000000</a>
Type	FMH1 S1/20V F1 B RL
GTIN (EAN)	4064675001249
Qty.	280 items
Product data	IEC: / 2.8 A UL: 150 V
Packaging	Tape

## FMH1 S1/20V F1 B RL

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate No. (cURus)	E92202

## Dimensions and weights

Depth	7.4 mm	Depth (inches)	0.2913 inch
Height	7.6 mm	Height (inches)	0.2992 inch
Width	17.78 mm	Width (inches)	0.7 inch
Net weight	5.6 g		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## System specifications

Product family	OMNIMATE Signal - Board-to-Board	Type of connection	Board connection
Mounting onto the PCB	SMD solder connection	Pitch in mm (P)	1.27 mm
Pitch in inches (P)	0.050 "	Outgoing elbow	180°
Number of poles	20	Number of solder pins per pole	1
Coplanarity:	0.1 mm	Number of rows	1
Pin series quantity	2	Protection degree	IP20
Volume resistance	<25 mΩ	Plugging cycles	500
Plugging force/pole, max.	0.6 N	Pulling force/pole, max.	0.6 N

## Material data

Insulating material	LCP	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	Illa
Insulation resistance	$\geq 10^{10} \Omega$	Moisture Level (MSL)	1
UL 94 flammability rating	V-0	Contact base material	Copper alloy
Contact material	Cu-alloy	Contact surface	Gold over nickel
Layer structure of plug contact	$\geq 2 \mu\text{m Ni} / \geq 0.4 \mu\text{m PdNi} / \geq 0.05 \mu\text{m Au}$	Storage temperature, min.	-40 °C
Storage temperature, max.	70 °C	Operating temperature, min.	-55 °C
Operating temperature, max.	125 °C		

## Rated data acc. to IEC

Rated current, min. number of poles (Tu=20°C)	2.8 A	Creepage distance, min.	0.4 mm
Clearance, min.	0.4 mm		

## Rated data acc. to UL 1977

Reference to approval values	Specifications are maximum values, details - see approval certificate.	Rated voltage (UL 1977) (obsolete)	150 V
------------------------------	--	------------------------------------	-------

**FMH1 S1/20V F1 B RL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Packing**

Packaging	Tape	VPE length	350.00 mm
VPE width	350.00 mm	VPE height	135.00 mm

**Important note**


IPC conformity      Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

Notes

**Classifications**


ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		

Product image




Dimensional drawing

Typ	No. of pins	Series	A	B	C	D	E	F	G
FMH1 S1/20V F1 B RL	12	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	15	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	20	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	25	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	30	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	35	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	40	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	45	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	50	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	60	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0
FMH1 S1/20V F1 B RL	70	FMH1	40.0	40.0	40.0	40.0	40.0	40.0	40.0



Detailed drawing



Derating curve

