

## VG M32 EXI 16-21 CR7J G4

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



Abbildung ähnlich

Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety).

Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, they are ATEX and IECEx certified.

### General ordering data

Version	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 32, 10 mm, OD min. 16 - OD max. 21 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	<a href="#">2722290000</a>
Type	VG M32 EXI 16-21 CR7J G4
GTIN (EAN)	4050118821529
Qty.	25 items

**VG M32 EXI 16-21 CR7J G4**
**Weidmüller Interface GmbH & Co. KG**

 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data**
**Approvals**

Approvals	CE
Approvals	CE; EAC; ATEX; IECEX; INMETRO
Approvals	



ROHS	Conform
------	---------

**Dimensions and weights**

Height	45.3 mm	Height (inches)	1.7835 inch
Length	42 mm	Length (inches)	1.6535 inch
Net weight	22 g		

**Temperatures**

Operating temperature	-40 °C...70 °C
-----------------------	----------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Certificate numbers cable gland**

Identification	Ex eb IIC Gb, Ex tb IIIC Db IP66/68	Certificate no. cable gland (ATEX)	IMQ 13 ATEX 010 X
Certificate no. cable gland (INMETRO)	DNV 18.0150 X/01	Certificate no. cable gland (IECEX)	IECEX IMQ 13.0003X
Approval conditions	ATEX, IECEX		

**General information**

Outer cable diameter, max.	21 mm	Outer cable diameter, min.	16 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	6 Nm
UL 94 flammability rating	HB	Operating temperature range, max.	70 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Halogen	Yes	Standards	IEC 60079-0, EN 60079-0, IEC 60079-7, EN 60079-7, EN 60079-31, IEC 60079-31
Impact resistance	7 joules in acc. with IEC 60079-0	AF size 1	36 mm
AF size 2	36 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Polyamide 6
Seal insert	CR	Sealing	CR
External thread	M 32	Length of thread	10 mm
Torque for cap nut, max.	7.00 Nm	Torque for connecting adapter, max.	7.00 Nm
Torque for connecting adapter, min.	5.00 Nm	Torque for cap nut, min.	5.00 Nm
Explosion protection type	Intrinsically safe Ex i	Installation guidelines	See assembly instructions

**Classifications**

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-02

**VG M32 EXI 16-21 CR7J G4**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data**

---

ECLASS 15.0

27-14-08-02

---

## VG M32 EXI 16-21 CR7J G4

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Plastic lock nuts, black



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

### General ordering data

Type	SKMU M32 K SW	Version	
Order No.	<a href="#">1736950000</a>	SKMU PA (plastic locknut), Locknut, M 32, 7 mm, Polyamid 6 (PA6 -	
GTIN (EAN)	4008190956424	GF30)	
Qty.	100 ST		