

VG M16 EXI 5-8 SI7J G4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

Polyamide cable glands, which are suitable for usage in explosion risk zones Ex e (increased safety) and Ex i (intrinsic safety).

Weidmüller offers a product family without restrictions and besides compliance with standards, the cable gland excels thanks to its increased impact resistance of 4/7 Joule and a possible temperature range down to -60°C without restrictions. They have been tested to the current standard and EN 60079-0 directive, they are ATEX and IECEx certified.

General ordering data

Version	VG Exi 7J (Ex plastic cable gland 7J Exi), Cable glands, straight, M 16, 10 mm, OD min. 5 - OD max. 8 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Polyamide 6
Order No.	2722360000
Type	VG M16 EXI 5-8 SI7J G4
GTIN (EAN)	4050118821598
Qty.	50 items


VG M16 EXI 5-8 SI7J G4

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals	CE
Approvals	CE; EAC; ATEX; IECEx; INMETRO
Approvals	

ROHS	Conform
------	---------

Dimensions and weights

Height	31.6 mm	Height (inches)	1.2441 inch
Length	26 mm	Length (inches)	1.0236 inch
Net weight	8 g		

Temperatures

Operating temperature	-60 °C...70 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Certificate numbers cable gland

Identification	Ex eb IIC Gb, Ex tb IIIC Db IP66/68	Certificate no. cable gland (ATEX)	IMQ 13 ATEX 010 X
Certificate no. cable gland (INMETRO)	DNV 18.0150 X/01	Certificate no. cable gland (IECEx)	IECEx IMQ 13.0003X
Approval conditions	ATEX, IECEx		

General information

Outer cable diameter, max.	8 mm	Outer cable diameter, min.	5 mm
Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Tightening torque	2.5 Nm
UL 94 flammability rating	HB	Operating temperature range, max.	70 °C
Operating temperature range, min.	-60 °C	Pitch of thread	1.5 mm
Halogen	No	Standards	IEC 60079-0, EN 60079-0, IEC 60079-7, EN 60079-7, EN 60079-31, IEC 60079-31
Impact resistance	7 joules in acc. with IEC 60079-0	AF size 1	19 mm
AF size 2	19 mm	Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Cable gland	metric	Basic material	Polyamide 6
Seal insert	Silicone	Sealing	Silicone
External thread	M 16	Length of thread	10 mm
Torque for cap nut, max.	3.00 Nm	Torque for connecting adapter, max.	3.00 Nm
Torque for connecting adapter, min.	2.00 Nm	Torque for cap nut, min.	2.00 Nm
Explosion protection type	Intrinsically safe Ex i	Installation guidelines	See assembly instructions

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-02

VG M16 EXI 5-8 SI7J G4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

ECLASS 15.0

27-14-08-02

VG M16 EXI 5-8 SI7J G4

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Plastic lock nuts, black



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	SKMU M16 K SW	Version	
Order No.	1736920000	SKMU PA (plastic locknut), Locknut, M 16, 5 mm, Polyamid 6 (PA6 -	
GTIN (EAN)	4008190956394	GF30)	
Qty.	100 ST		