

**IE-S1DS2VE0150T01T01-E****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)**SPElink**<sup>®</sup>

Single pair Ethernet is a technology that only requires one pair of wires to transmit data and power.

The resulting benefits will make SPE the preferred network at the field level and beyond. Advantages of Single Pair Ethernet

- Consistent: Single Pair Ethernet enables uniform Ethernet-based communication from the sensor to the cloud
- Future-proof: key technology for Industry 4.0 and IIoT
- Flexible: ranges of up to 1000 m and transmission properties of up to 1 Gbps enable use across applications
- Innovative: lighter, less space required, and reduced installation effort

**General ordering data**

Version	Patch cable, SPE plug (IEC 63171-2) - IP20 socket contact straight, SPE plug (IEC 63171-2) - IP20 socket contact straight, T1-B, PVC, 15 m
Order No.	<a href="#">2725850150</a>
Type	IE-S1DS2VE0150T01T01-E
GTIN (EAN)	4064675364658
Qty.	1 items
Delivery status	Discontinued
Last order date	2026-03-27T00:00:00+01:00
Alternative product	<a href="#">IE-S1DS2VE0150T02T02-E</a>

## IE-S1DS2VE0150T01T01-E

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E316369

### Dimensions and weights

Length	15 m	Length (inches)	590.5512 inch
Net weight	200 g		

### Temperatures

Storage temperature	Operating temperature	-40 °C...80 °C
Installation temperature		

### Environmental Product Compliance

RoHS Compliance Status Compliant without exemption

REACH SVHC No SVHC above 0.1 wt%

### Electrical properties

Dielectric strength, contact / shield	2250 V DC	Dielectric strength, contact / contact	1000 V DC
PoE / PoE+	PoDL acc. to IEEE 802.3bu / cg		

### Standards

Connector standard IEC 63171-2

### Cable structure

Strands	7	Sheathing colour	black
Cross-section	2*AWG 22	Shielding	STP
Number of wires	2	Insulation	PE
Sheath diameter, max.	5.3 mm	Sheath diameter, min.	4.9 mm
Material sheath	PVC	Colour coding	white / blue
Complete shielding	Shielding braid made from copper wiring	Overlap of shielding braid	80 %
Insulation diameter 2	1.65 mm		

### Electrical properties of cable

Rated voltage (DC)	60 V	Transmission rate	10/100 MBit/s, 1000 MBit/s
Category	T1-B	Nominal current	3.5 A
Coupling attenuation 1 to 600 MHz	Type I	Test voltage: wire-wire-shield	1 kV DC, 1 min
Capacity at 800 Hz	1.6 nF/km	Resistance differential	2 %
Characteristic impedance	100 ± 15 Ω at 20 MHz		

**Technical data**

**Mechanical and material properties of cable**

Resistance to oils	IRM 902/903 oil resistance test at (70°Cx4h)	UV-resistant	Complies with UL 1581 Sec. 1200
Colour	black	Halogen	Yes
Bending radius	20 mm	Resistance to spread of flame	FT1

**Plug**

Plug right	SPE, IP20, female contact, straight, plug, Plastic, shielded	Plug left	SPE, IP20, female contact, straight, plug, Plastic, shielded
------------	--	-----------	--

**Plug, left**

Plug left	SPE, IP20, female contact, straight, plug, Plastic, shielded
-----------	--

**Plug, right**

Plug right	SPE, IP20, female contact, straight, plug, Plastic, shielded
------------	--

**Classifications**

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

**Detailed drawing**

**Dimensional drawing**

