

## IE-S1DS2VE0100TM1TM1-E

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



SPElink®



Single pair Ethernet is a technology that only requires one pair of wires to transmit data and power.

The resulting benefits will make SPE the preferred network at the field level and beyond. Advantages of Single Pair Ethernet

- Consistent: Single Pair Ethernet enables uniform Ethernet-based communication from the sensor to the cloud
- Future-proof: key technology for Industry 4.0 and IIoT
- Flexible: ranges of up to 1000 m and transmission properties of up to 1 Gbps enable use across applications
- Innovative: lighter, less space required, and reduced installation effort

### General ordering data

Version	Patch cable, M8 SPE ( IEC63171-5) - IP67 socket contact - straight, M8 SPE ( IEC63171-5) - IP67 socket contact - straight, T1-B, PVC, 10 m
Order No.	<a href="#">2726050100</a>
Type	IE-S1DS2VE0100TM1TM1-E
GTIN (EAN)	4064675597452
Qty.	1 items

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Length	10 m	Length (inches)	393.7008 inch
Net weight	335 g		

**Temperatures**

Storage temperature	Operating temperature	-40 °C...85 °C
Installation temperature		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Electrical properties**

Dielectric strength, contact / shield	2250 V DC	
Dielectric strength, contact / contact	1000 V DC	
Current-carrying capacity	Current-carrying capacity	3.5 A
	Temperature	0 °C
PoE / PoE+	PoDL acc. to IEEE 802.3bu / cg	

**Standards**

Connector standard	IEC 63171-5
--------------------	-------------

**Cable structure**

Strands	7	Sheathing colour	black
Cross-section	2*AWG 22	Shielding	STP
Number of wires	2	Insulation	PE
Sheath diameter, max.	5.3 mm	Sheath diameter, min.	4.9 mm
Material sheath	PVC	Colour coding	white / blue
Complete shielding	Shielding braid made from copper wiring	Overlap of shielding braid	80 %
Insulation diameter 2	1.65 mm		

**Electrical properties of cable**

Rated voltage (DC)	60 V	Transmission rate	10/100 MBit/s, 1000 MBit/s
Category	T1-B	Nominal current	3.5 A
Coupling attenuation 1 to 600 MHz	Type I	Test voltage: wire-wire-shield	1 kV DC, 1 min
Capacity at 800 Hz	1.6 nF/km	Resistance differential	2 %
Characteristic impedance	100 ± 15 Ω at 20 MHz		

**IE-S1DS2VE0100TM1TM1-E**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Mechanical and material properties of cable**

Resistance to oils	IRM 902/903 oil resistance test at (70°Cx4h)	UV-resistant	Complies with UL 1581 Sec. 1200
Colour	black	Halogen	Yes
Resistance to spread of flame	FT1		

**Plug**

Plug right	M8, Number of poles: 2, IP67, female contact, straight, Plastic, IEC 63171-5, shielded	Plug left	M8, Number of poles: 2, IP67, female contact, straight, Plastic, IEC 63171-5, shielded
------------	--	-----------	--

**Plug, left**

Plug left	M8, Number of poles: 2, IP67, female contact, straight, Plastic, IEC 63171-5, shielded
-----------	--

**Plug, right**

Plug right	M8, Number of poles: 2, IP67, female contact, straight, Plastic, IEC 63171-5, shielded
------------	--

**Classifications**

ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

**IE-S1DS2VE0100TM1TM1-E**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Drawings**

[www.weidmueller.com](http://www.weidmueller.com)

