

DEK 5/8 PLUS FS 1-50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
- Strips for fast installation
- Terminal markers, suitable for all Weidmüller cable connectors
- Available as blank MultiCard or with standard printing

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

| | |
|------------|------------------------------------------------------------------------------|
| Version | Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00 Weidmueller, white |
| Order No. | 2748100000 |
| Type | DEK 5/8 PLUS FS 1-50 |
| GTIN (EAN) | 4050118891454 |
| Qty. | 800 items |

DEK 5/8 PLUS FS 1-50

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Dimensions and weights

| | | | |
|------------|--------|-----------------|-------------|
| Height | 5 mm | Height (inches) | 0.1968 inch |
| Width | 8 mm | Width (inches) | 0.315 inch |
| Net weight | 0.08 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...100 °C |
|-----------------------------|--------------|

Environmental Product Compliance

| | | | |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status | Compliant without exemption | | |
| REACH SVHC | No SVHC above 0.1 wt% | | |
| Product Carbon Footprint | Cradle to gate | 0,001 kg CO2 eq. | |

General data

| | | | |
|--------------------------------------|-------------------------------|-----------|--|
| Orientation of print | vertical | | |
| Width | 8 mm | | |
| UL 94 flammability rating | V-2 | | |
| Operating temperature range, max. | 100 °C | | |
| Operating temperature range, min. | -40 °C | | |
| Colour | white | | |
| Halogen | No | | |
| Basic material | Polyamide 66 | | |
| Colour of printing | black | | |
| Printed characters | Numbers | | |
| Number of markers per packaging unit | Form of supply | MultiCard | |
| Number of markers per combination | 1 MultiCard = Terminal marker | | |
| Operating temperature range | -40...100 °C | | |
| Application/manufacturer | Weidmueller | | |

Connector markers

| | |
|-----------------|---------|
| Pitch in mm (P) | 8.00 mm |
|-----------------|---------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000761 | ETIM 9.0 | EC000761 |
| ETIM 10.0 | EC000761 | ECLASS 14.0 | 27-28-11-01 |
| ECLASS 15.0 | 27-28-11-01 | | |

Drawings



Drawing

