

WPD 111 1X95/4X35 RD

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Our WPD 1XX distribution blocks are used in all situations where power is supplied and distributed. Their user-friendly design creates a better overview and enables Rapid, efficient implementation of space-saving power distribution.

General ordering data

Version	Potential distributor terminal, Screw connection, red, 95 mm ² , 232 A, 1000 V, Number of connections: 5, Number of levels: 1
Order No.	2730310000
Type	WPD 111 1X95/4X35 RD
GTIN (EAN)	4050118844955
Qty.	1 items

WPD 111 1X95/4X35 RD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E60693
Certificate no. (cULus)	E511333

Dimensions and weights

Depth	69.4 mm	Depth (inches)	2.7323 inch
Height	105 mm	Height (inches)	4.1338 inch
Width	36.6 mm	Width (inches)	1.4409 inch
Net weight	240 g		

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	130 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	9b5f0838-1f0b-4c14-9fc7-3f5e6ee75be2

Material data

Basic material	Wemid	Colour	red
UL 94 flammability rating	V-0		

System specifications

Version	Screw connection	End cover plate required	No
Number of potentials	1	Number of levels	1
Number of clamping points per level	5	Levels cross-connected internally	No
Mounting rail	TS 35, Mounting plate	N-function	No
PE function	No	PEN function	No

Additional technical data

Open sides	closed	Snap-on	Yes
Explosion-tested version	Yes	Type of mounting	Snap-on, Direct mounting

Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection
--	------------------

Conductors for clamping (rated connection)

Wire connection cross section AWG, max.	AWG 4/0	Connection direction	on side
Type of connection 2	Screw connection	Type of connection	Screw connection

WPD 111 1X95/4X35 RD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Number of connections	5	Clamping range, max.	95 mm ²
Clamping range, min.	2.5 mm ²	Wire connection cross section AWG, min.	AWG 8
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	2.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	70 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	2.5 mm ²	Wire connection cross section, finely stranded, max.	0 mm ²
Wire connection cross section, finely stranded, min.	2.5 mm ²	Connection cross-section, stranded, max.	95 mm ²
Connection cross-section, stranded, min.	2.5 mm ²	Wire connection cross-section, solid core, max.	95 mm ²
Wire connection cross-section, solid core, min.	2.5 mm ²		

General

Number of poles	1	Wire connection cross section AWG, max.	AWG 4/0
Wire connection cross section AWG, min.	AWG 8	Standards	IEC 60947-7-1
Mounting rail	TS 35, Mounting plate		

Rating data

Rated cross-section	95 mm ²	Rated voltage	1000 V
Rated AC voltage	1000 V	Rated DC voltage	1500 V
Nominal current	232 A	Current at maximum wires	232 A
Standards	IEC 60947-7-1	Rated impulse withstand voltage	8 kV
Surge voltage category	III	Pollution severity	3

UL rating data

Certificate No. (cURus)	E60693
-------------------------	--------

Important note

Product information	The socket complies with flammability class V-2 according to UL94.
---------------------	--

Classifications

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-19
ECLASS 15.0	27-25-01-19		

WPD 111 1X95/4X35 RD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Drawings

www.weidmueller.com



Conductor connection data according to IEC 60947-1 (Cu)

connection point A		connection point A	
Input	Copper	Output	Copper
1x 95 mm²	14 Nm	1x 35 mm²	6 Nm
95 mm²	14 Nm	35 mm²	6 Nm
70 mm²		25 mm²	
50 mm²		18 mm²	
35 mm²		10 mm²	
25 mm²		6 mm²	
16 mm²		4 mm²	
10 mm²		2.5 mm²	
Stripping lengths	21 mm	Stripping lengths	10 mm
Allen screw	M12	Allen screw	M8



Conductor connection data according to 1059 (Al+Cu)

connection point A		connection point 1 / 2 / 3 / 4	
Input (line)	Copper	Aluminum	Aluminum
AWG 4/0			
AWG 3/0			
AWG 2/0	200 lb. In.	200 lb. In.	124.8 lb. In.
AWG 1/0			
AWG 1			
AWG 2			
AWG 3			
AWG 4			
AWG 6			
AWG 8			
max. current	230 A	200 A	180 A
max. current			155 A
Voltage size IEC 609	1000 V		

