

HDC MHS 25 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Version	Power module, 30 V, 4 A, Number of poles: 25, Crimp connection, Male, Required plug-in slots: 1
Order No.	2748500000
Type	HDC MHS 25 MC
GTIN (EAN)	4050118890914
Qty.	5 items

HDC MHS 25 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E92202
Certificate No. (cURus)	E310075

Dimensions and weights

Depth	14.6 mm	Depth (inches)	0.5748 inch
Height	34 mm	Height (inches)	1.3386 inch
Width	34.2 mm	Width (inches)	1.3465 inch
Length	14.6 mm	Length (inches)	0.5748 inch
Net weight	8.5 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Number of poles	25	UL 94 flammability rating	V-0
Plugging cycles	≥ 500	Type	Male
Surge voltage category	III	Pollution severity	3
Basic material	Polycarbonate	Series	ModuPlug
Rated voltage (DIN EN 61984)	30 V	Rated impulse voltage (DIN EN 61984)	0.8 kV
Rated current (DIN EN 61984)	4 A	Required plug-in slots	1

PE connection data

Connection type PE Screw connection via module frame

Version

Wire connection cross section AWG, max.	AWG 28	Type of connection	Crimp connection
Wire connection cross section AWG, min.	AWG 20	Conductor cross-section, max.	0.5 mm ²
Conductor cross-section, min.	0.08 mm ²		

Power contact

Rated impulse voltage (DIN EN 61984), power contact 0.8 kV

Tightening torque, max. according to the conductor cross-section	Conductor cross-section, min.	0.08 mm ²
	Conductor cross-section, max.	0.5 mm ²

HDC MHS 25 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Stripping length according to the cable diameter	Cable diameter, min.	2.2 mm
	Stripping length	4.20 mm

Signal contact

Rated voltage (DIN EN 61984), signal contact	30 V	Rated impulse voltage (DIN EN 61984), signal	0.8 kV
Rated current (DIN EN 61984), signal	4 A		

Classifications



ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-17
ECLASS 15.0	27-44-02-17		

HDC MHS 25 MC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC MHS 25 MC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Standard



General ordering data

Type	HDC MF 6B AB	Version
Order No.	1428920000	Frame
GTIN (EAN)	4050118233414	
Qty.	1 ST	
Type	HDC MF 6B BA	Version
Order No.	1428940000	Frame
GTIN (EAN)	4050118233353	
Qty.	1 ST	
Type	HDC MF 10B AC	Version
Order No.	1428960000	Frame
GTIN (EAN)	4050118233223	
Qty.	1 ST	
Type	HDC MF 10B CA	Version
Order No.	1428980000	Frame
GTIN (EAN)	4050118233278	
Qty.	1 ST	
Type	HDC MF 16B AD	Version
Order No.	1429010000	Frame
GTIN (EAN)	4050118233315	
Qty.	1 ST	
Type	HDC MF 16B DA	Version
Order No.	1429030000	Frame
GTIN (EAN)	4050118233407	
Qty.	1 ST	
Type	HDC MF 24B AF	Version
Order No.	1429050000	Frame
GTIN (EAN)	4050118233285	
Qty.	1 ST	
Type	HDC MF 24B FA	Version
Order No.	1429070000	Frame
GTIN (EAN)	4050118233520	
Qty.	1 ST	

HDC MHS 25 MC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

D-SUB crimp contacts



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC C HS BM0.08-0.12 AU	Version
Order No.	2748730000	Female, gold, 0.08 - 0.12 mm ²
GTIN (EAN)	4050118890549	
Qty.	100 ST	
Type	HDC C HS BM0.2-0.5 AU	Version
Order No.	2748720000	Female, gold, 0.2 - 0.5 mm ²
GTIN (EAN)	4050118890631	
Qty.	100 ST	
Type	HDC C HS SM0.08-0.12 AU	Version
Order No.	2748710000	Male, gold, 0.08 - 0.12 mm ²
GTIN (EAN)	4050118890556	
Qty.	100 ST	
Type	HDC C HS SM0.2-0.5 AU	Version
Order No.	2748700000	Male, gold, 0.2 - 0.5 mm ²
GTIN (EAN)	4050118890709	
Qty.	100 ST	