

**HDC C COAX 75 M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

**General ordering data**

Version	Male, gold
Order No.	<a href="#">2748690000</a>
Type	HDC C COAX 75 M
GTIN (EAN)	4050118890648
Qty.	10 items

**HDC C COAX 75 M**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Length	23 mm	Length (inches)	0.9055 inch
Net weight	2.4 g		

**Temperatures**

Limit temperature -55 °C ... 135 °C

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	6eabd5ae-2d6b-409e-8bdf-87c27ee10e40

**General data**

Contact diameter, male Ø	4.8 mm	Stripping length, rated connection	2.5 mm
Type of connection	Solder connection	Version insert	COAX
Colour	gold	Surface finish	gold
Plugging cycles	≥ 500	Type	Male
Basic material	Copper alloy	Production methods	turned

**Classifications**

ETIM 8.0	EC000796	ETIM 9.0	EC000796
ETIM 10.0	EC000796	ECLASS 14.0	27-44-02-04
ECLASS 15.0	27-44-02-04		