

IE-CSPD5UD0030LSSVAP-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

Version	System cable, M12 L-code – IP 67 straight socket, PushPull Power, PUR, 3 m
Order No.	2732640030
Type	IE-CSPD5UD0030LSSVAP-X
GTIN (EAN)	4064675022008
Qty.	1 items
Delivery status	Discontinued
Available until	2024-02-27T00:00:00+01:00

IE-CSPD5UD0030LSSVAP-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Length	3 m	Length (inches)	118.1102 inch
Net weight	300 g		

Temperatures

Storage temperature	Operating temperature	-25 °C...75 °C
Installation temperature		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Cable specific standards

Standard, sheathing material	20939 (80 °C / 600 V)
------------------------------	-----------------------

Electrical properties

Nominal voltage	24 V	Rated current	16 A
-----------------	------	---------------	------

General standards

Connector standard	in accordance with PROFINET specification, IEC 61076-2-111
--------------------	--

Standards

Standard, sheathing material	20939 (80 °C / 600 V)	Connector standard	in accordance with PROFINET specification, IEC 61076-2-111
------------------------------	-----------------------	--------------------	--

Cable structure

Sheathing colour	Silver grey	Cross-section	5*1.5 mm ²
Shielding	unshielded	Number of wires	5
Insulation	PP	Sheath diameter, max.	8.2 mm
Sheath diameter, min.	7.8 mm	Material sheath	PUR
Colour coding	brown, white, blue, black, pink		

Mechanical and material properties of cable

Halogen	No	Acceleration	5 m/s ²
Min. bending radius, repetitive	7.5 x cable diameter	Min. bending radius, once only	4 x cable diameter

Plug

Plug right	PushPull Power, IP67, female contact, straight,	Plug left	M12, L-coded, IP67, male contact, straight, plug, Plastic, unshielded
------------	--	-----------	---

IE-CSPD5UD0030LSSVAP-X**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data**plug, Zinc diecast,
unshielded**Plug, left**

Plug left

M12, L-coded, IP67, male
contact, straight, plug,
Plastic, unshielded**Plug, right**

Plug right

PushPull Power, IP67,
female contact, straight,
plug, Zinc diecast,
unshielded**Classifications**

ETIM 8.0

EC003248

ETIM 9.0

EC003248

ETIM 10.0

EC003248

ECLASS 14.0


27-06-01-05

ECLASS 15.0

27-06-01-05

IE-CSPD5UD0030LSSVAP-X
Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com
Accessories
Blank


TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility.

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	TM-I 12 MC NE WS	Version
Order No.	1718411044	TM-I, Insert markers, 12 x 4 mm, white
GTIN (EAN)	4008190348977	
Qty.	320 ST	
Type	TM-I 18 MC NE WS	Version
Order No.	1718431044	TM-I, Insert markers, 1.5 - 22 mm, 18 x 4 mm, white
GTIN (EAN)	4008190349011	
Qty.	320 ST	