

KCMA-8-1000-5A-5VA-0.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Current transformers for retrofitting

Features:

- especially suitable for use in hard-to-reach places
- no cutting of the primary conductors necessary
- Unfolding of the current transformer without additional tools

General ordering data

Version	Primary current: 1000 A, Secondary current max.: 5 A, Load: 5 VA, Tolerance class: 0,5, Split-core current transformer
Order No.	2753430000
Type	KCMA-8-1000-5A-5VA-0.5
GTIN (EAN)	4050118896565
Qty.	1 items
Manufacturer	MBS AG

KCMA-8-1000-5A-5VA-0.5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	58 mm	Depth (inches)	2.2835 inch
Height	198 mm	Height (inches)	7.7953 inch
Width	155 mm	Width (inches)	6.1024 inch
Net weight	1300 g		

Temperatures

Storage temperature	Operating temperature	-5 °C...40 °C
---------------------	-----------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	80.00 mm
Rail	80 x 120 mm	Installation location	Indoor use

Electrical attributes

Tolerance class	0,5	Secondary current	0...5 A
Load	5 VA	Primary current	1000 A

Technical properties

Cable length	0.5 m	Protection degree	IP20
Insulation class	E	Thermal rated continuous current I _{thermal}	1.2 x I _{rated}
Nominal frequency	50 Hz		

Insulation coordination

Standard	IEC 61869-1: 2007, IEC 61869-2: 2012	Tolerance class	0,5
----------	---	-----------------	-----

Classifications

ETIM 8.0	EC002048	ETIM 9.0	EC002048
ETIM 10.0	EC002048	ECLASS 14.0	27-21-09-02
ECLASS 15.0	27-21-09-02		

KCMA-8-1000-5A-5VA-0.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

