


**CC-DT-H 30/60 BL****Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26  
D-32758 Detmold  
Germany[www.weidmueller.com](http://www.weidmueller.com)

We support our customers in the food industry with detectable marking solutions to ensure the high standards required within the framework of the HACCP concept. Thanks to a metallic filler, our detectable MultiCards can be reliably identified by metal and X-ray detectors. This minimises the risk of product contamination in the production process. Maximum safety is ensured with important product properties, such as corrosion resistance or higher ageing resistance to UV radiation in indoor areas and heat. These properties are regularly tested and confirmed in our own accredited laboratory.

Not suitable for direct food contact.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler
- Clear and resistant print image
- Available in different versions for a wide variety of marking requirements

**General ordering data**

Version	ClipCard, Accessories, 30 x 63.8 mm, blue
Order No.	<a href="#">2737760000</a>
Type	CC-DT-H 30/60 BL
GTIN (EAN)	4064675211792
Qty.	10 items

## CC-DT-H 30/60 BL

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Approvals

RoHS	Conform
------	---------

## Dimensions and weights

Depth	6 mm	Depth (inches)	0.2362 inch
Height	30 mm	Height (inches)	1.1811 inch
Width	63.8 mm	Width (inches)	2.5118 inch
Net weight	4.12 g		

## Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%
Product Carbon Footprint	Cradle to gate 0.046 kg CO2 eq.

## General data

Version	Marker holder
Width	63.8 mm
UL 94 flammability rating	HB
Operating temperature range, max.	100 °C
Operating temperature range, min.	-40 °C
Colour	blue
Halogen	No
Basic material	Polyamide 66
Number of markers per packaging unit	Form of supply
Detectable in accordance with Rondotest 4.7 mm Al	MultiCard
Recommended industries	Food processing industry
Number of markers per combination	1 MultiCard = Accessories
Operating temperature range	-40...100 °C

## Device markers

Halogen	No
---------	----

## Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

**CC-DT-H 30/60 BL**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**


## CC-DT-H 30/60 BL

Weidmüller Interface GmbH & Co. KG  
Klingenbergsstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Accessories



We support our customers in the food industry with detectable marking solutions to ensure the high standards required within the framework of the HACCP concept. Thanks to a metallic filler, our detectable MultiCards can be reliably identified by metal and X-ray detectors. This minimises the risk of product contamination in the production process. Maximum safety is ensured with important product properties, such as corrosion resistance or higher ageing resistance to UV radiation in indoor areas and heat. These properties are regularly tested and confirmed in our own accredited laboratory. Not suitable for direct food contact.

- Detectable by metal and X-ray detectors
- Visually recognisable by blue colour
- Corrosion resistant metallic filler
- Clear and resistant print image
- Available in different versions for a wide variety of marking requirements

## General ordering data

Type	CC-DT-H 30/60 BL	Version
Order No.	<a href="#">2737760000</a>	ClipCard, Accessories, 30 x 63.8 mm, blue
GTIN (EAN)	4064675211792	
Oty.	10 ST	