


**ATTB 6 PG CT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In T&D applications, current and voltage transformers are mainly used for protection and measurement functions. Our TTB range of Klippon® Connect instrument transformer terminal blocks have been designed to meet all the connection requirements of these two critical applications. The wiring of current and voltage transformers can be carried out particularly easily and safely with the new terminal block series – even within complex circuits. The prevention of operating errors during operation increases plant availability and extends the life cycle of the entire control cabinet. Thus, the respective requirements of the end user are fulfilled to the highest degree.

**General ordering data**

Version	Test-disconnect terminal, PUSH IN, 6 mm <sup>2</sup> , 500 V, 30 A, dark beige
Order No.	<a href="#">2762280000</a>
Type	ATTB 6 PG CT
GTIN (EAN)	4064675267676
Qty.	50 items

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

## Dimensions and weights

Depth	68 mm	Depth (inches)	2.6772 inch
Height	109 mm	Height (inches)	4.2913 inch
Width	8.1 mm	Width (inches)	0.3189 inch
Net weight	30.66 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60 °C
Continuous operating temp., max.	130 °C		

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## Material data

Basic material	Wemid	Colour	dark beige
Colour of operational elements	orange	UL 94 flammability rating	V-0

## System specifications

End cover plate required	Yes	Number of potentials	1
Number of levels	1	Number of clamping points per level	2
Number of potentials per tier	1	Levels cross-connected internally	No
Mounting rail	TS 35		

## Additional technical data

Open sides	right	Type of mounting	TS 35
------------	-------	------------------	-------

## CSA rating data

Wire cross section max. (CSA)	8 AWG	Certificate No. (CSA)	200039-80099474
Voltage size D (CSA)	300 V	Current size D (CSA)	10 A
Wire cross section min. (CSA)	22 AWG		

## Conductors for clamping (additional connection)

Connection type, additional connection pluggable

## ATTB 6 PG CT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A5	Wire connection cross section AWG, max.	AWG 8
Connection direction	top	Stripping length	12 mm
Type of connection	PUSH IN	Number of connections	2
Clamping range, max.	10 mm <sup>2</sup>	Clamping range, min.	0.5 mm <sup>2</sup>
Blade size	0.8 x 4.0 mm	Wire connection cross section AWG, min.	AWG 22
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	6 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	10 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	10 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	0.5 mm <sup>2</sup>
Connection cross-section, stranded, max.	6 mm <sup>2</sup>	Connection cross-section, stranded, min.	0.5 mm <sup>2</sup>
Wire connection cross-section, solid core, max.	6 mm <sup>2</sup>	Wire connection cross-section, solid core, min.	0.5 mm <sup>2</sup>

## General

Wire connection cross section AWG, max.	AWG 8	Wire connection cross section AWG, min.	AWG 22
Standards	IEC 60947-7-1	Mounting rail	TS 35

## Rating data

Rated cross-section	6 mm <sup>2</sup>	Rated voltage	500 V
Rated DC voltage	500 V	Nominal current	30 A
Current at maximum wires	30 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	0.78 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC 60947-7-x	1.31 W	Surge voltage category	III
Pollution severity	3		




## UL rating data

Conductor size Factory wiring max. (cURus)	8 AWG	Voltage size D (cURus)	300 V
Certificate No. (cURus)	E60693	Conductor size Field wiring min. (cURus)	22 AWG
Conductor size Factory wiring min. (cURus)	22 AWG	Current size D (cURus)	10 A
Conductor size Field wiring max. (cURus)	8 AWG		

## Classifications

ETIM 8.0	EC000902	ETIM 9.0	EC000902
ETIM 10.0	EC000902	ECLASS 14.0	27-25-01-09
ECLASS 15.0	27-25-01-09		

Drawings



## ATTB 6 PG CT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

## Accessorie



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

## General ordering data

Type	TS TTB 6 BK	Version
Order No.	<a href="#">2710520000</a>	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
GTIN (EAN)	4050118881080	
Qty.	48 ST	
Type	TS TTB 6 BL	Version
Order No.	<a href="#">2710480000</a>	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
GTIN (EAN)	4050118880656	
Qty.	48 ST	
Type	TS TTB 6 BR	Version
Order No.	<a href="#">2715540000</a>	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
GTIN (EAN)	4050118769609	
Qty.	48 ST	
Type	TS TTB 6 GN	Version
Order No.	<a href="#">2710490000</a>	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
GTIN (EAN)	4050118880953	
Qty.	48 ST	
Type	TS TTB 6 OR	Version
Order No.	<a href="#">2710470000</a>	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
GTIN (EAN)	4050118880649	
Qty.	48 ST	
Type	TS TTB 6 RD	Version
Order No.	<a href="#">2710510000</a>	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
GTIN (EAN)	4050118881073	
Qty.	48 ST	
Type	TS TTB 6 VT	Version
Order No.	<a href="#">2710530000</a>	Socket (terminal), Plug-in depth: 11.5 mm, 0.00 mm, Depth: 51.3 mm
GTIN (EAN)	4050118881097	
Qty.	48 ST	
Type	TS TTB 6 WT	Version
Order No.	<a href="#">2817250000</a>	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
GTIN (EAN)	4064675322566	
Qty.	48 ST	
Type	TS TTB 6 YL	Version
Order No.	<a href="#">2710500000</a>	Socket (terminal), Plug-in depth: 11.5 mm, Depth: 51.3 mm
GTIN (EAN)	4050118881066	
Qty.	48 ST	
Type	SL TTB 6	Version
Order No.	<a href="#">2710220000</a>	Lockout device (terminal), PA 66/6, red
GTIN (EAN)	4050118893311	
Qty.	50 ST	

## ATTB 6 PG CT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	LL TTB 6/1	Version
Order No.	<a href="#">2710230000</a>	Locking lever (terminal)
GTIN (EAN)	4050118847925	
Qty.	50 ST	
Type	LL TTB 6/1 BK	Version
Order No.	<a href="#">2710280000</a>	Locking lever (terminal)
GTIN (EAN)	4050118847963	
Qty.	50 ST	
Type	LL TTB 6/1 BL	Version
Order No.	<a href="#">2710240000</a>	Locking lever (terminal)
GTIN (EAN)	4050118847918	
Qty.	50 ST	
Type	LL TTB 6/1 BR	Version
Order No.	<a href="#">2762590000</a>	Locking lever (terminal)
GTIN (EAN)	4064675018377	
Qty.	50 ST	
Type	LL TTB 6/1 GN	Version
Order No.	<a href="#">2710250000</a>	Locking lever (terminal)
GTIN (EAN)	4050118847949	
Qty.	50 ST	
Type	LL TTB 6/1 RD	Version
Order No.	<a href="#">2710270000</a>	Locking lever (terminal)
GTIN (EAN)	4050118847956	
Qty.	50 ST	
Type	LL TTB 6/1 VT	Version
Order No.	<a href="#">2710290000</a>	Locking lever (terminal)
GTIN (EAN)	4050118847970	
Qty.	50 ST	
Type	LL TTB 6/1 WT	Version
Order No.	<a href="#">2817220000</a>	Locking lever (terminal)
GTIN (EAN)	4064675322535	
Qty.	50 ST	
Type	LL TTB 6/1 YL	Version
Order No.	<a href="#">2710260000</a>	Locking lever (terminal)
GTIN (EAN)	4050118893335	
Qty.	50 ST	
Type	LL TTB 6/2	Version
Order No.	<a href="#">2710300000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848243	
Qty.	50 ST	
Type	LL TTB 6/2 BK	Version
Order No.	<a href="#">2710350000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848274	
Qty.	50 ST	
Type	LL TTB 6/2 BL	Version
Order No.	<a href="#">2710310000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848250	
Qty.	50 ST	
Type	LL TTB 6/2 BR	Version
Order No.	<a href="#">2762600000</a>	Locking lever (terminal)
GTIN (EAN)	4064675018384	
Qty.	50 ST	

## ATTB 6 PG CT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	LL TTB 6/2 CM	Version
Order No.	<a href="#">2710370000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012092	
Qty.	50 ST	
Type	LL TTB 6/2 CM BK	Version
Order No.	<a href="#">2710420000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012641	
Qty.	50 ST	
Type	LL TTB 6/2 CM BL	Version
Order No.	<a href="#">2710380000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012603	
Qty.	50 ST	
Type	LL TTB 6/2 CM BR	Version
Order No.	<a href="#">2762610000</a>	Locking lever (terminal)
GTIN (EAN)	4064675018391	
Qty.	50 ST	
Type	LL TTB 6/2 CM GN	Version
Order No.	<a href="#">2710390000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012610	
Qty.	50 ST	
Type	LL TTB 6/2 CM RD	Version
Order No.	<a href="#">2710410000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012634	
Qty.	50 ST	
Type	LL TTB 6/2 CM VT	Version
Order No.	<a href="#">2710430000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012658	
Qty.	50 ST	
Type	LL TTB 6/2 CM WT	Version
Order No.	<a href="#">2817240000</a>	Locking lever (terminal)
GTIN (EAN)	4064675322559	
Qty.	50 ST	
Type	LL TTB 6/2 CM YL	Version
Order No.	<a href="#">2710400000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012627	
Qty.	50 ST	
Type	LL TTB 6/2 GN	Version
Order No.	<a href="#">2710320000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848328	
Qty.	50 ST	
Type	LL TTB 6/2 RD	Version
Order No.	<a href="#">2710340000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848281	
Qty.	50 ST	
Type	LL TTB 6/2 VT	Version
Order No.	<a href="#">2710360000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848267	
Qty.	50 ST	
Type	LL TTB 6/2 WT	Version
Order No.	<a href="#">2817230000</a>	Locking lever (terminal)
GTIN (EAN)	4064675322542	
Qty.	50 ST	

## ATTB 6 PG CT


**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	LL TTB 6/2 YL	Version
Order No.	<a href="#">2710330000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848311	
Qty.	50 ST	
Type	LL TTB 6/3	Version
Order No.	<a href="#">2710440000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848236	
Qty.	50 ST	
Type	LL TTB 6/3 CM	Version
Order No.	<a href="#">2726100000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012665	
Qty.	50 ST	
Type	LL TTB 6/4	Version
Order No.	<a href="#">2710450000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848229	
Qty.	25 ST	
Type	LL TTB 6/4 CM	Version
Order No.	<a href="#">2726110000</a>	Locking lever (terminal)
GTIN (EAN)	4064675012672	
Qty.	50 ST	
Type	LL TTB 6/6	Version
Order No.	<a href="#">2710460000</a>	Locking lever (terminal)
GTIN (EAN)	4050118848212	
Qty.	10 ST	

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

Type	AEB 35 SCL/1 V0	Version
Order No.	<a href="#">2661280000</a>	A-series, End bracket
GTIN (EAN)	4050118702163	
Qty.	20 ST	
Type	AEB 35 SCL/1 V0 BK	Version
Order No.	<a href="#">2661300000</a>	A-series, End bracket
GTIN (EAN)	4050118702187	
Qty.	20 ST	
Type	AEB 35 SCL/1 V0 GY	Version
Order No.	<a href="#">2661290000</a>	A-series, End bracket
GTIN (EAN)	4050118702170	
Qty.	20 ST	

## ATTB 6 PG CT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

### Accessorie



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

### General ordering data

Type	SCCB TTB 6/2	Version
Order No.	<a href="#">2710190000</a>	Cross-connector (terminal), Plugged, orange, 30 A, Number of poles:
GTIN (EAN)	4050118847987	2, Pitch in mm (P): 8.10, Insulated: Yes, Width: 16 mm
Qty.	25 ST	
Type	SCCB TTB 6/3	Version
Order No.	<a href="#">2710200000</a>	Cross-connector (terminal), Plugged, orange, 30 A, Number of poles:
GTIN (EAN)	4050118847994	3, Pitch in mm (P): 8.10, Insulated: Yes, Width: 24.1 mm
Qty.	25 ST	
Type	SCCB TTB 6/4	Version
Order No.	<a href="#">2710210000</a>	Cross-connector (terminal), Plugged, orange, 30 A, Number of poles:
GTIN (EAN)	4050118848007	4, Pitch in mm (P): 8.10, Insulated: Yes, Width: 32.2 mm
Qty.	25 ST	

### Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

Type	ZQV 6N/10	Version
Order No.	<a href="#">2733970000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4064675066811	10, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm
Qty.	20 ST	
Type	ZQV 6N/6	Version
Order No.	<a href="#">2733950000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4064675066699	6, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm
Qty.	20 ST	
Type	ZQV 6N/7	Version
Order No.	<a href="#">2733960000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4064675066804	7, Pitch in mm (P): 8.00, Insulated: Yes, Width: 3.1 mm
Qty.	20 ST	

## ATTB 6 PG CT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

## Accessories

www.weidmueller.com

## Accessorie



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

## General ordering data

Type	CH TTB	Version
Order No.	<a href="#">2710130000</a>	Cover hood (terminal)
GTIN (EAN)	4064675021155	
Qty.	1 ST	
Type	CP TTB	Version
Order No.	<a href="#">2710140000</a>	Cover hood (terminal)
GTIN (EAN)	4064675014171	
Qty.	10 ST	
Type	CS TTB	Version
Order No.	<a href="#">2710150000</a>	A-series, End bracket
GTIN (EAN)	4064675021148	
Qty.	10 ST	

## DEK 5/8



## WS/ DEK

MultiMark terminal markers use an innovative composite material made from two components. The hard base contour of the marker snaps securely into the connector. The elastic surface finish makes the marker easy to mount. This specially punched material enables the strips to be stretched to accommodate the slight variations in spacing that tend to add up, especially with long terminal blocks. Another advantage: the excellent printability of the surface material guarantees durable and wear-resistant labelling. A print resolution of 300 dpi also produces a very legible script.

Your benefits with MultiMark

- Firm hold and durable printing
- Continuous strips save installation time
- Easy mounting thanks to an innovative composite material
- Large label field for optimal legibility
- High flexibility thanks to manufacturer independence

## General ordering data

Type	DEK-A 5/8 MM WS	Version
Order No.	<a href="#">2448860000</a>	Dekafix, Terminal marker, 5 x 8.1 mm, Weidmueller, white
GTIN (EAN)	4050118462968	
Qty.	500 ST	

## ATTB 6 PG CT

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

## Accessories

www.weidmueller.com

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

Type	DEK 5/8-11.5 MC NE WS	Version
Order No.	<a href="#">1341630000</a>	Dekafix, Terminal marker, 5 x 8 mm, Pitch in mm (P): 8.00
GTIN (EAN)	4050118145946	Weidmueller, white
Qty.	500 ST	

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	ZQV 6N/10 BL	Version
Order No.	<a href="#">2786910000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 10, Pitch in mm (P): 8.00, Insulated: Yes, Width: 78.7 mm
GTIN (EAN)	4064675064602	
Qty.	20 ST	
Type	ZQV 6N/2	Version
Order No.	<a href="#">1985740000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: 2, Pitch in mm (P): 8.00, Insulated: Yes, Width: 13.7 mm
GTIN (EAN)	4050118370362	
Qty.	60 ST	
Type	ZQV 6N/3	Version
Order No.	<a href="#">1985760000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles: 3, Pitch in mm (P): 8.00, Insulated: Yes, Width: 21.8 mm
GTIN (EAN)	4050118370263	
Qty.	60 ST	
Type	ZQV 6N/3 BL	Version
Order No.	<a href="#">1985840000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 3, Pitch in mm (P): 8.00, Insulated: Yes, Width: 21.8 mm
GTIN (EAN)	4050118370379	
Qty.	60 ST	

## ATTB 6 PG CT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	ZQV 6N/4	Version
Order No.	<a href="#">1985780000</a>	Cross-connector (terminal), Plugged, orange, 41 A, Number of poles:
GTIN (EAN)	4050118370287	4, Pitch in mm (P): 8.00, Insulated: Yes, Width: 29.9 mm
Qty.	60 ST	
Type	ZQV 6N/4 BL	Version
Order No.	<a href="#">1985850000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 4,
GTIN (EAN)	4050118370447	Pitch in mm (P): 8.00, Insulated: Yes, Width: 29.9 mm
Qty.	60 ST	
Type	ZQV 6N/6 BL	Version
Order No.	<a href="#">2786890000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 6,
GTIN (EAN)	4064675064572	Pitch in mm (P): 8.00, Insulated: Yes, Width: 46.3 mm
Qty.	20 ST	
Type	ZQV 6N/7 BL	Version
Order No.	<a href="#">2786900000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 7,
GTIN (EAN)	4064675064596	Pitch in mm (P): 8.00, Insulated: Yes, Width: 54.4 mm
Qty.	20 ST	

## Accessorie



The comprehensive accessories of the Klippon® Connect TTB-Range are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms. All function- and safety-relevant components are captively connected to the terminal block. This increases the reliability of the current and voltage transformer circuits during installation and maintenance work.

## General ordering data

Type	AEP TTB 6 PG	Version
Order No.	<a href="#">2762310000</a>	A-series, End plate
GTIN (EAN)	4064675075899	
Qty.	20 ST	

## Plugs



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

## General ordering data

Type	APG 6/2 MBB	Version
Order No.	<a href="#">2762330000</a>	Plug, 6 mm <sup>2</sup> , 500 V, 30 A, Number of poles: 2, dark beige
GTIN (EAN)	4064675021339	
Qty.	20 ST	

## ATTB 6 PG CT

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

Type	APG 6/3 MBB	Version
Order No.	<a href="#">2762340000</a>	Plug, 6 mm <sup>2</sup> , 500 V, 30 A, Number of poles: 3, dark beige
GTIN (EAN)	4064675021346	
Qty.	20 ST	
Type	APGSR 6	Version
Order No.	<a href="#">2762390000</a>	Strain relief (terminal), Wemid, orange
GTIN (EAN)	4064675021391	
Qty.	20 ST	
Type	APGLE 6	Version
Order No.	<a href="#">2762400000</a>	Locking element (terminal), Wemid, orange
GTIN (EAN)	4064675021407	
Qty.	20 ST	
Type	APGCE	Version
Order No.	<a href="#">1514490000</a>	Coding element (terminal), Wemid, orange, Width: 3.3 mm
GTIN (EAN)	4050118321906	
Qty.	50 ST	

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

Type	ZQV 6N/2 BL	Version
Order No.	<a href="#">1985830000</a>	Cross-connector (terminal), Plugged, blue, 41 A, Number of poles: 2,
GTIN (EAN)	4050118370232	Pitch in mm (P): 8.00, Insulated: Yes, Width: 13.7 mm
Qty.	60 ST	

## Plugs



The plugs for our WeiCoS-System are available for all different connection systems. The product range includes preassembled connectors from 1 to 10 poles and the possibility of an individual assembly. This ensures maximum flexibility for every application. The customized accessories increase the safety and protection against environmental influences.

## General ordering data

Type	APGPC 6	Version
Order No.	<a href="#">2762410000</a>	Cover hood (terminal)
GTIN (EAN)	4064675021414	
Qty.	20 ST	

## ATTB 6 PG CT

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Testadapter and testsockets



Test adapters and test plugs are used for the electrical connection between terminal blocks and the test equipment. In this way, an electrical contact can be established in the wired state and measurements can be done easily.

### General ordering data

Type	FZS 2/4 RT/80 SAKT4	Version	
Order No.	<a href="#">1276300000</a>	Plug (terminal), Plug-in connection, 2 mm <sup>2</sup> , Number of connections: 2,	
GTIN (EAN)	4008190026080	Number of poles: 1, Width: 9 mm	
Qty.	20 ST		