


**PAC-S1500-SD15-V3-1M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|            |                                   |
|------------|-----------------------------------|
| Version    | Cable LiYCY, 0.25 mm <sup>2</sup> |
| Order No.  | <a href="#">2740930010</a>        |
| Type       | PAC-S1500-SD15-V3-1M              |
| GTIN (EAN) | 4099986604735                     |
| Qty.       | 1 items                           |

**PAC-S1500-SD15-V3-1M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |       |
|------------|-------|
| Net weight | 204 g |
|------------|-------|

**Temperatures**

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

**Environmental Product Compliance**

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

**General Data**

|                     |                      |                       |                                             |
|---------------------|----------------------|-----------------------|---------------------------------------------|
| Cable length        | 1 m                  | Suitable for          | Analogue signals                            |
| Basic material      | PVC                  | Cable                 | Cable LiYCY                                 |
| Interface connector | SUB-D FEMALE 15P     | Number of poles, min. | 15-pole                                     |
| Outer diameter      | 8.7 ± 1 mm           | Connector PLC side    | SIEMENS S71500<br>6ES7592-1AM00-0XB0<br>40P |
| Wire cross-section  | 0.25 mm <sup>2</sup> |                       |                                             |

**Electrical Data**

|                          |           |                                             |          |
|--------------------------|-----------|---------------------------------------------|----------|
| Total current, max.      | 3 A       | Permissible current strength per path, max. | 1 A      |
| Resistance               | ≤ 80 mΩ/m | Capacity (wire / wires)                     | 300 pF/m |
| Capacity (wire / shield) | 300 pF/m  |                                             |          |

**Rated data UL**

|                     |     |
|---------------------|-----|
| Total current, max. | 3 A |
|---------------------|-----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |