

**JB 25-50 TH****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Our potential equalisation terminal blocks allow you to achieve reliably integrated potential equalisation, even in extended systems.

**General ordering data**

Version	Potential distributor terminal, Screw connection, Brass coloured, 50 mm <sup>2</sup> , 0 A, Number of connections: 2, Number of levels: 1
Order No.	<a href="#">2762660000</a>
Type	JB 25-50 TH
GTIN (EAN)	4064675267706
Qty.	10 items

## JB 25-50 TH

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (UR) E60693

## Dimensions and weights

Depth	24 mm	Depth (inches)	0.9449 inch
Height	32 mm	Height (inches)	1.2598 inch
Width	33 mm	Width (inches)	1.2992 inch
Net weight	50 g		

## Temperatures

Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C
----------------------------------	--------	----------------------------------	--------

## Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption		
RoHS Exemption (if applicable/known)	6c		
REACH SVHC	Lead 7439-92-1		
SCIP	233a6569-7068-4d0c-aa40-90d1ca672d0b		

## Material data

Basic material	Brass	Colour	Brass coloured
UL 94 flammability rating	None		

## System specifications

End cover plate required	No	Number of potentials	1
Number of levels	1	Number of clamping points per level	2
Levels cross-connected internally	No	PE connection	Yes
Mounting rail	Mounting plate	PE function	Yes

## Additional technical data

Explosion-tested version	No	Type of mounting	when screwed in
--------------------------	----	------------------	-----------------

## Conductors for clamping (additional connection)

Connection type, additional connection Screw connection

## Conductors for clamping (rated connection)

Wire connection cross section AWG, max.	AWG 1	Connection direction	on side
Tightening torque, max.	3 Nm	Stripping length	33 mm
Type of connection 2	Screw connection	Type of connection	Screw connection
Number of connections	2	Clamping range, max.	50 mm <sup>2</sup>

## JB 25-50 TH

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

Clamping range, min.	10 mm <sup>2</sup>	Clamping screw	M 4
Wire connection cross section AWG, min.	AWG 8	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	10 mm <sup>2</sup>
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	50 mm <sup>2</sup>	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	10 mm <sup>2</sup>
Wire connection cross section, finely stranded, max.	50 mm <sup>2</sup>	Wire connection cross section, finely stranded, min.	10 mm <sup>2</sup>
Connection cross-section, stranded, max.	50 mm <sup>2</sup>	Connection cross-section, stranded, min.	10 mm <sup>2</sup>
Wire connection cross-section, solid core, max.	50 mm <sup>2</sup>	Wire connection cross-section, solid core, min.	10 mm <sup>2</sup>

### General

Wire connection cross section AWG, max.	AWG 1	Wire connection cross section AWG, min.	AWG 8
Standards	IEC 60947-7-2	Mounting rail	Mounting plate

### Rating data

Rated cross-section	50 mm <sup>2</sup>	Nominal current	0 A
Standards	IEC 60947-7-2	Pollution severity	3

### UL rating data

Certificate No. (UR)	E60693
----------------------	--------

### Classifications

ETIM 8.0	EC000897	ETIM 9.0	EC000897
ETIM 10.0	EC000897	ECLASS 14.0	27-25-01-19
ECLASS 15.0	27-25-01-19		