

## MHS 5/06 D11 H T3 B T



**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



OMNIMATE® 4.0 - the next evolution step  
OMNIMATE® 4.0 follows the trend of One Cable Technology (OCT). The modular concept enables the fast configuration of hybrid interfaces, which transmit data, signals and energy in a single connector. As a result, you can reduce the cabling effort in a wide variety of applications, simplify maintenance and accelerate automation processes. The unique SNAP IN connection is the backbone and speeds up the wiring process.

The fastest connection yet

- Fast, safe, and tool-free wiring due to unique SNAP IN connection
- Ready for Robot through "wire ready" delivery with open clamping point
- Optical and acoustic feedback indicates proper wiring

Create your own configuration

- Flexible configuration and ordering via the Weidmüller Configurator (WMC)
- Dispatch within three days – even for individually configured products
- Automatic offer preparation for the configured product

Simply configuration of modular hybrid connectors

- Flexible combination options for power, signal and data transmission
- Future-proof Single-Pair Ethernet technology

### General ordering data

Version	PCB plug-in connector, male header, THT/THR solder connection, Pitch in mm (P): 5.00 mm, Number of poles: 6, 90°, Tube
Order No.	<a href="#">2741550000</a>
Type	MHS 5/06 D11 H T3 B T
GTIN (EAN)	4064675055525
Qty.	13 items
Product data	IEC: 400 V / 26.8 A UL: 300 V / 18.5 A
Packaging	Tube

## MHS 5/06 D11 H T3 B T

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

ROHS	Conform
------	---------

## Dimensions and weights

Depth	14.8 mm	Depth (inches)	0.5827 inch
Height	15.1 mm	Height (inches)	0.5945 inch
Height of lowest version	11.9 mm	Width	39.7 mm
Width (inches)	1.563 inch	Net weight	12.28 g

## Temperatures

Ambient temperature	-50 °C...125 °C
---------------------	-----------------

## Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

## System specifications

Product family	OMNIMATE 4.0	Type of connection	Board connection
Mounting onto the PCB	THT/THR solder connection	Pitch in mm (P)	5.00 mm
Pitch in inches (P)	0.197 "	Outgoing elbow	90°
Number of poles	6	Number of solder pins per pole	1
Solder pin length (l)	3.2 mm	Solder pin dimensions	1.0 x 1.0 mm
Solder eyelet hole diameter (D)	1.4 mm	Solder eyelet hole diameter tolerance (D)+	0,1 mm
Outside diameter of solder pad	2.3 mm	Template aperture diameter	2.1 mm
L1 in mm	25.00 mm	L1 in inches	0.984 "
Number of rows	1	Pin series quantity	1
Touch-safe protection acc. to DIN VDE 57 106	Touch-safe above the printed circuit board	Touch-safe protection acc. to DIN VDE 0470	IP 20
Protection degree	IP20	Volume resistance	≤5 mΩ
Plugging force/pole, max.	8.5 N	Pulling force/pole, max.	8.5 N

## Material data

Insulating material	PA 9T	Colour	black
Colour chart (similar)	RAL 9011	Insulating material group	I
Comparative Tracking Index (CTI)	≥ 600	Moisture Level (MSL)	1
UL 94 flammability rating	V-0	Contact base material	CuMg
Contact material	Cu-alloy	Contact surface	tinned
Tinning type	mat	Storage temperature, min.	-25 °C
Storage temperature, max.	55 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C		

## Rated data acc. to IEC

tested acc. to standard	IEC 60664-1, IEC 61984	Rated current, min. number of poles (Tu=20°C)	26.8 A
Rated current, max. number of poles (Tu=20°C)	19.7 A	Rated current, min. number of poles (Tu=40°C)	23.1 A
Rated current, max. number of poles (Tu=40°C)	16.9 A	Rated voltage for surge voltage class / pollution degree II/2	400 V
Rated voltage for surge voltage class / pollution degree III/2	320 V	Rated voltage for surge voltage class / pollution degree III/3	250 V

## MHS 5/06 D11 H T3 B T

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

### Technical data

Rated impulse voltage for surge voltage class/ pollution degree II/2	4 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	4 kV
Clearance, min.	4 mm

Rated impulse voltage for surge voltage class/ pollution degree III/2	4 kV
Creepage distance, min.	5.4 mm

#### Rated data acc. to UL 1059

Rated voltage (Use group B / UL 1059)	300 V
Rated voltage (Use group F / UL 1059)	420 V
Rated current (Use group D / UL 1059)	10 A
Clearance distance, min.	4 mm

Rated voltage (Use group D / UL 1059)	300 V
Rated current (Use group B / UL 1059)	18.5 A
Creepage distance, min.	5.6 mm

#### Technical data - hybrid (data)

Number of poles (Data)	2
Contact material (Data)	Cu
Rated current (Data)	2 A
Solder pin length (l) (Data)	2.1 mm
Tolerance of solder pin position (Data)	0.1 mm
Dielectric strength, contact / shield (Data)	≥ 1500 V DC
PoE / PoE+ (Data)	PoDL acc. to IEEE 802.3bu / cg
Shielding (Data)	Yes

Connector Standard (Data)	IEC 63171-2
Contact surface (Data)	Ni/Au
Rated voltage (Data)	72 V
Solder pin dimensions (Data)	Octagonal
Dielectric strength, contact / contact (Data)	≥ 1000 V DC
Insulation strength (Data)	≥ 500 MΩ
Transmission rate (Data)	10/100 MBit/s, 1000 MBit/s

#### Technical data - hybrid (power)

Number of rows (Signal)	1
-------------------------	---

#### Technical data - hybrid (signal)

Number of poles (Signal)	6
Contact material (Signal)	CuMg
Rated current (Use group B / UL 1059) (Signal)	18.5 A
Rated current, min. number of poles (Tu=20°C) (Signal)	26.8 A
Rated current, min. number of poles (Tu=40°C) (Signal)	23.1 A
Rated voltage (Use group B / UL 1059) (Signal)	300 V
Rated voltage for surge voltage class / pollution degree II/2 (Signal)	400 V
Rated voltage for surge voltage class / pollution degree III/3 (Signal)	250 V
Rated impulse voltage for surge voltage class/ pollution degree III/2 (Signal)	4 kV
Volume resistance (Signal)	≤5 mΩ
Clearance distance, min. (Signal)	4 mm
Solder pin dimensions (Signal)	1.0 x 1.0 mm
Diameter of solder eyelet (Signal)	1.4 mm
Template aperture diameter (Signal)	2.1 mm

Number of solder pins per pole (Signal)	1
Contact surface (Signal)	tinned
Rated current (Use group D / UL 1059) (Signal)	10 A
Rated current, max. number of poles (Tu=20°C) (Signal)	19.7 A
Rated current, max. number of poles (Tu=40°C) (Signal)	16.9 A
Rated voltage (Use group D / UL 1059) (Signal)	300 V
Rated voltage for surge voltage class / pollution degree III/2 (Signal)	320 V
Rated impulse voltage for surge voltage class/ pollution degree II/2 (Signal)	4 kV
Rated impulse voltage for surge voltage class/ pollution degree III/3 (Signal)	4 kV
Creepage distance, min. (Signal)	5.4 mm
Solder pin length (Signal)	3.2 mm
Tolerance of the diameter of the solder eyelet (Signal)	+ 0,1 mm
Outside diameter of solder pad (Signal)	2.3 mm

#### Important note

IPC conformity

Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp.

## MHS 5/06 D11 H T3 B T

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

### Notes

- Rated current related to rated cross-section & min. No. of poles.
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Diameter of solder eyelet D = 1.4+0.1mm
- In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
- Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

### Classifications

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-02-01
ECLASS 15.0	27-46-02-01		

MHS 5/06 D11 H T3 B T

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

Drawings

www.weidmueller.com

