

**VPUM2I2SXFV201TXPX10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com



PV Protect is the solution for optimum protection of the inverter against overvoltages. It is very compact and only requires Y-cables to connect to the PV strings. So it is a perfect product to retrofit existing PV residential installations with overvoltage protection.

**General ordering data**

Version	Surge protection, 2 MPP's, Surge protection II, WM4C, 1000 V
Order No.	<a href="#">2764130000</a>
Type	VPUM2I2SXFV201TXPX10
GTIN (EAN)	4064675016106
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-03-31T00:00:00+02:00
Alternative product	<a href="#">PVI DC 1I 1O 2MPP SPD1 MC4 10</a>

**VPUM2I2SXFV201TXPX10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Approvals**

Approvals



ROHS Conform

**Dimensions and weights**

Depth	91 mm	Depth (inches)	3.5827 inch
Height	160 mm	Height (inches)	6.2992 inch
Width	168 mm	Width (inches)	6.6142 inch
Net weight	860 g		

**Temperatures**

Storage temperature	-40 °C...85 °C	Ambient temperature	-40 °C...85 °C
Operating temperature	-40 °C...85 °C	Humidity	5 - 95% rel. humidity

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**Approvals and norms**

Approvals EN 50539-11

**Enclosure**

Enclosure attachment	Via the four holes under the cover screws	Connection type string	Plug WM4C
----------------------	---	------------------------	-----------

**General data**

Standards	EN 50539-11	Protection degree	IP67
-----------	-------------	-------------------	------

**Inputs**

Amount of maximum power points (MPP)	2 MPP		
Functional earth connector	Cable entry	Number of cable entries	1
	Wire connection	Type of connection	PUSH IN
DC Input + & -	Wire connection	Type of connection	WM4 C field connector
	Cable entry	Number of cable entries	2
Fuse type	Neither fuse cartridge nor holder		
Number of string inputs per MPP	1		

**Surge protection DC side**

Standards	EN 50539-11	Discharge current, max. (8/20 µs)	40 kA
Protection level Up (+/- , -/PE , +/-PE)	≤4,2 kV	Conditions and requirements	EN 50539-11

**VPUM2I2SXFV201TXPX10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

Operating height in ungrounded PV system	≤ 4000 m	Short-circuit current ISCPV	11 kA
Total discharge current I <sub>total</sub> (8/20µs)	50 kA	Discharge current I <sub>n</sub> (8/20 µs)	20 kA
Requirements class	Type II	Operating height in the grounded PV system	≤ 4000 m
PV system voltage, max. U <sub>cpv</sub>	1100 V	Maximum continuous operating voltage DC UCPV mode +/-, -/PE, +/PE	1100 V

**Important note**

Product information                      The SPD in the box cannot be replaced.

**Classifications**

ETIM 8.0	EC000941	ETIM 9.0	EC000941
ETIM 10.0	EC000941	ECLASS 14.0	27-17-14-02
ECLASS 15.0	27-17-14-02		

**Tender specification sheets**

Long specification                      Designation 2: VPU PV BOX WM4 II 5 1000 2M  
 Over voltage protection box for inverters with 2Mpp tracker, used to protect the DC side.  
 Max. String voltage U<sub>oc</sub>: 1000 V MPPT1: 1 input, connection via WM4 C plug-in connector, compatible with cable type TÜV 2 Pfg1 169/08.07 / EN 50618:2069 MPPT 2 is identical to MPPT 1 Connection of the box in stitch without DC switch 2 surge protection type II Connection of functional earth via cable glands (8-12mmØ) cable cross-section: 16mm<sup>2</sup> Protection class: IP65 and IP67 Plastic enclosure Dimensions HxWxD: 168x160x91 mm According to standard, EN 50539-11: 2013+A1:2014 IEC 61643-31: 2018

**VPUM2I2SXXFXV2O1TXPX10**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany


www.weidmueller.com

Drawings

Connection diagram



Connection diagram



<b>Series</b> PVN = PV Next VPU = PV Protect	<b>Voltage</b> 10 = 1kV 11 = 1,1kV 15 = 1,5kV
<b>Level</b> 1 = DC trunk box (L1)	<b>Powersupply</b> x = n/a
<b>Series</b> 1 = 1 MPPT supported 2 = 2 MPPT supported 3 = 3 MPPT supported 4 = 4 MPPT supported 6 = 6 MPPT supported	<b>Monitoring</b> x = n/a
<b>Inputs</b> 1...12 inputs	<b>Output Type</b> 0 = CG 1 = WM4C 2 = MC4-Evo 2
<b>Switch</b> x = n/a 0 = manual switch 1 = remote switch	<b>SPD</b> 2/0 = TYP II 1 = TYP I+II X = No SPD
	<b>Fuses</b> x = n/a 3 = only fuse holders