


A2T 2.5 DT/FT BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



In some applications it makes sense to add a test point or a disconnect element to the feed through terminal for testing and safety purposes. With test disconnect terminals you measure electric circuits in the absence of voltage. While the disconnecting points clearance and creepage distance is not assessed in dimensional terms, the specified rated impulse voltage strength must be proven.

General ordering data

| | |
|------------|--|
| Version | Test-disconnect terminal, PUSH IN, 2.5 mm ² , 400 V, 16 A, blue |
| Order No. | 2744140000 |
| Type | A2T 2.5 DT/FT BL |
| GTIN (EAN) | 4064675035336 |
| Qty. | 50 items |

A2T 2.5 DT/FT BL

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 50.5 mm | Depth (inches) | 1.9882 inch |
| Height | 115 mm | Height (inches) | 4.5275 inch |
| Width | 5.1 mm | Width (inches) | 0.2008 inch |
| Net weight | 18.35 g | | |

Temperatures

| | | | |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C | | |

Environmental Product Compliance

| | |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

Material data

| | | | |
|--------------------------------|--------|---------------------------|------|
| Basic material | Wemid | Colour | blue |
| Colour of operational elements | orange | UL 94 flammability rating | V-0 |

Rating data IECEX/ATEX

| | | | |
|-------------------------|------------------|---------------------------------|---------------------|
| Certificate No. (IECEX) | IECEXTUR16.0045U | Max. voltage (IECEX) | 400 V |
| Current (IECEX) | 20 A | Wire cross section max. (IECEX) | 2.5 mm ² |

System specifications

| | | | |
|--------------------------|-------|-------------------------------------|----|
| End cover plate required | Yes | Number of potentials | 2 |
| Number of levels | 2 | Number of clamping points per level | 2 |
| Mounting rail | TS 35 | N-function | No |
| PE function | No | PEN function | No |

Additional technical data

| | | | |
|---------|-----|------------------|---------|
| Snap-on | Yes | Type of mounting | Snap-on |
|---------|-----|------------------|---------|

Conductors for clamping (rated connection)

| | |
|---|----------------------|
| Gauge to IEC 60947-1 | A3 |
| Wire connection cross section AWG, max. | AWG 12 |
| Connection direction | top |
| Stripping length | 10 mm |
| Type of connection | PUSH IN |
| Number of connections | 4 |
| Clamping range, max. | 4 mm ² |
| Clamping range, min. | 0.14 mm ² |

A2T 2.5 DT/FT BL

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

| | | | |
|---|--|---------|----------------------|
| Blade size | 0.6 x 3.5 mm | | |
| Wire connection cross section AWG, min. | AWG 28 | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm ² | | |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm ² | | |
| Wire connection cross section, finely stranded, max. | 2.5 mm ² | | |
| Wire connection cross section, finely stranded, min. | 0.5 mm ² | | |
| Connection cross-section, stranded, max. | 2.5 mm ² | | |
| Connection cross-section, stranded, min. | 0.5 mm ² | | |
| Wire connection cross-section, solid core, max. | 2.5 mm ² | | |
| Wire connection cross-section, solid core, min. | 0.5 mm ² | | |
| Tube length for wire-end ferrule without plastic collar DIN 46228/1 | Tube length | nominal | 5 mm |
| | Cross-section for conductor connection | nominal | 0.25 mm ² |
| | | min. | 6 mm |
| | Tube length | max. | 10 mm |
| | | min. | 0.5 mm ² |
| | Cross-section for conductor connection | max. | 1 mm ² |
| | | min. | 7 mm |
| | Tube length | max. | 12 mm |
| | | min. | 1.5 mm ² |
| | Cross-section for conductor connection | max. | 4 mm ² |

General

| | | | |
|---|---------------|---|--------|
| Wire connection cross section AWG, max. | AWG 12 | Wire connection cross section AWG, min. | AWG 28 |
| Standards | IEC 60947-7-1 | Mounting rail | TS 35 |

Rating data

| | | | |
|---------------------------------|---------------------|------------------------|---------------|
| Rated cross-section | 2.5 mm ² | Rated voltage | 400 V |
| Rated DC voltage | 400 V | Nominal current | 16 A |
| Current at maximum wires | 16 A | Standards | IEC 60947-7-1 |
| Rated impulse withstand voltage | 6 kV | Surge voltage category | III |
| Pollution severity | 3 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000902 | ETIM 9.0 | EC000902 |
| ETIM 10.0 | EC000902 | ECLASS 14.0 | 27-25-01-09 |
| ECLASS 15.0 | 27-25-01-09 | | |

Drawings

