


CH20M6 BP 4P-4P BUS BK LF 1 1261494**Weidmüller Interface GmbH & Co. KG**Klingenbergsstraße 26
D-32758 Detmold
Germanywww.weidmueller.com**Product image**

The basic element of the modular CH20M housing offers a number of advantages that make it an excellent choice for your projects. With special cut-outs for bus and FE contacts, it is particularly flexible and adaptable.

Another plus point is the option of laser printing on the housing, which offers you high precision and individual design options. A wide range of colors is also available so that you can design the housing entirely according to your wishes.

The CH20M housing is also suitable for standard mounting rails, which makes installation and integration into existing systems easier.

General ordering data

Version	Modular housing, OMNIMATE Housing - series CH20M black, Housing base, Recess in detent foot area for BUS contact, Width: 6.1 mm
Order No.	2771430000
Type	CH20M6 BP 4P-4P BUS BK LF 1 1261494
GTIN (EAN)	4064675032168
Qty.	50 items

CH20M6 BP 4P-4P BUS BK LF 1 1261494

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

RoHS	Conform
------	---------

Dimensions and weights

Depth	114.3 mm	Depth (inches)	4.5 inch
Height	110.7 mm	Height (inches)	4.3583 inch
Width	6.1 mm	Width (inches)	0.2402 inch
Net weight	2.34 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

UL 94 flammability rating	V-0	Insulating material	PBT
Insulating material group	II	Surface finish	untreated
Basic material	Plastic	Comparative Tracking Index (CTI)	400 ≤ CTI <600

General data

Colour	black	Protection degree	IP20 in installed state
Mounting rail	TS 35	Colour chart (similar)	RAL 9011
Encapsulation option	No		

Assembly properties

Number of PCBs, max.	1	Number of connection levels, max.	8
Number of poles, max.	8	Height of components on the PCB, max.	3.5 mm
Type of assembly of the PCB	one-sided		

Mechanical tests

According to Standard	DIN EN 61373:1999 (shock and vibration)		
Test conditions	50g additional weight on the PCB, with endbrackets WEW 35/1 (1059000000), four housings installed in a row		
Proved axles	X, Y, Z		
Shock test	General test advices	All mechanical tests were tested on exemplary setup, or in view of depending regulation. The specified results do not replace approval relevant tests. They are just orientation values.	
	Test category	1	
	Number of shocks per axle	3 in positive and negative direction	
	Shock duration	30 ms	
	Acceleration horizontal	50.00 m/s ²	
	Acceleration vertical	50.00 m/s ²	
	Acceleration longitudinal	50.00 m/s ²	
Vibration test	Test category	1B	
	Test duration	5 hours per axle	
	Effective acceleration	7.9 m/s ²	

CH20M6 BP 4P-4P BUS BK LF 1 1261494

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Component properties**

Cut out in clip-on foot area as preparation for	BUS-contact, contact not included!	Number of connection levels, max.	8
---	------------------------------------	-----------------------------------	---

Design - IN requirements

Tolerance for the PCB shape	± 0.1 mm	PCB thickness	0.8 mm
Tolerance of circuit board thickness	± 0.1 mm		

Individualization options

Customer specific cutouts possible	Yes	Customer specific labelling possible	Yes
Customer specific order process	See guideline under downloads	Alternative colours	More on request




Classifications

ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 14.0	27-19-06-01
ECLASS 15.0	27-19-06-01		


CH20M6 BP 4P-4P BUS BK LF 1 1261494

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings**Product image****Product image****Product benefits**

Base element including BUS cut-out

Dimensioned drawing

CH20M6 BP 4P-4P BUS BK LF 1 1261494

Weidmüller Interface GmbH & Co. KG
 Klingenbergsstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories**CH20M6 C - Flip cover**

The Flip cover of the CH20M housing offers practical functions that support your application. It can be sealed, which ensures additional security and protection for your contents. You also have the option of printing on the cover using pad printing to clearly display important information or logos.

In addition, markers can be used to apply specific instructions or markings directly on the cover.

General ordering data

Type	CH20M6 C BK 1819	Version
Order No.	2418620000	Modular housing, OMNIMATE Housing - series CH20M black, transparent, Flip cover, Width: 6.1 mm
GTIN (EAN)	4032248899142	
Qty.	50 ST	
Type	CH20M6 C TP 8089	Version
Order No.	1073410000	Modular housing, OMNIMATE Housing - series CH20M Transparent, Flip cover, Width: 6.1 mm
GTIN (EAN)	4032248831203	
Qty.	50 ST	

SR-SMD - Bus contact block CH20M6

The integrated rail bus for the modular electronics housing system

When supplying, connecting or distributing within modular applications, the rail bus can replace the tedious individual wiring process with a flexible and uninterrupted system-wide solution.

The system bus is securely integrated within the 35-mm standard mounting rail. The SMD-bus contact block can be reflow-soldered so that it can be completely automatically processed during the component assembly. The resistant, gold-plated contact surfaces ensure a permanent and reliable contact for all housing widths.

- Unlimited scalability The integrated connection solution covers all system widths: from the 6-mm slice to the 67-mm large-area housing.
- Easy to service during installation It's easy to replace a module, even in existing modules groups – without any influence on the neighbouring modules.
- Universal integration The uninterrupted system bus is securely integrated within the 35-mm standard mounting rail.
- Maximum availability Five fully-galvanized and partially gold-plated twin-arched contacts are used to establish a permanent contact to the rail bus. THR solder flanges ensure that the connection to the circuit board is stable.

General ordering data

Type	SR-SMD 4.50/05/90 AU BK...	Version
Order No.	1155840000	PCB plug-in connector, Bus-contact block for CH20M6, THT/THR
GTIN (EAN)	4032248942534	solder connection, Number of poles: 5, 180°, Gold-plated, black
Qty.	78 ST	

CH20M6 BP 4P-4P BUS BK LF 1 1261494

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	SR-SMD 4.50/05/90 AU BK...	Version
Order No.	1155850000	PCB plug-in connector, Bus-contact block for CH20M6, THT/THR
GTIN (EAN)	4032248942374	solder connection, Number of poles: 5, 180°, Gold-plated, black
Qty.	300 ST	

LHZ-SMT L - left connection side



Naturally, the CH20M system also shows its detailed perfection in the peripheral interface.

If you are taking into consideration design options, processing, usability, reliability and security, then pin headers and connectors are just as critical in the real world as the entire system.

In every sector, the connection technology is at the top of its class.

- 100% safe protected against accidental touch
- 100% efficient fully compatible with reflow soldering
- 100% time and cost savings During the installation: the quick all-purpose "Multi-Tool" screw head ensures a secure contact, user-friendly operation and less complexity. Additional features, such as the "Wire ready" technology, enable you to minimize wiring costs and increase customer satisfaction.

General ordering data

Type	LHZ-SMT L 1.5SN BK BX	Version
Order No.	1137870000	Printed circuit board terminals, Connection element, left, block
GTIN (EAN)	4032248919741	assembly, closed side, THR solder connection, 0.00 mm, Number of poles: 1, Solder pin length (l): 1.5 mm, tinned, black, Box
Qty.	306 ST	
Type	LHZ-SMT L 1.5SN BK RL	Version
Order No.	2418580000	Printed circuit board terminals, Connection element, left, block
GTIN (EAN)	4032248984350	assembly, closed side, THR solder connection, 0.00 mm, Number of poles: 1, Solder pin length (l): 1.5 mm, tinned, black, Tape
Qty.	432 ST	

LHZ-SMT R - right connection side



Naturally, the CH20M system also shows its detailed perfection in the peripheral interface.

If you are taking into consideration design options, processing, usability, reliability and security, then pin headers and connectors are just as critical in the real world as the entire system.

In every sector, the connection technology is at the top of its class.

- 100% safe protected against accidental touch
- 100% efficient fully compatible with reflow soldering
- 100% time and cost savings During the installation: the quick all-purpose "Multi-Tool" screw head ensures a secure contact, user-friendly operation and less complexity. Additional features, such as the "Wire ready" technology, enable you to minimize wiring costs and increase customer satisfaction.

CH20M6 BP 4P-4P BUS BK LF 1 1261494

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories**General ordering data**

Type	LHZ-SMT R 1.5SN BK BX	Version
Order No.	1137880000	Printed circuit board terminals, Connection element, right, block
GTIN (EAN)	4032248919734	assembly, closed side, THR solder connection, 0.00 mm, Number of
Qty.	306 ST	poles: 1, Solder pin length (l): 1.5 mm, tinned, black, Box
Type	LHZ-SMT R 1.5SN BK RL	Version
Order No.	2418590000	Printed circuit board terminals, Connection element, right, block
GTIN (EAN)	4032248984343	assembly, closed side, THR solder connection, 0.00 mm, Number of
Qty.	432 ST	poles: 1, Solder pin length (l): 1.5 mm, tinned, black, Tape

CH20M6 BP 4P-4P BUS BK LF 1 1261494

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Counterpart

CH20M6 BC BUS - Housing side panel including preparation for busconnector



The world of electronics in a disk
With a width of just 6.1 mm, the electronics developer's expertise creates compact application worlds. Specially developed for a PCB, the modular housing concept offers ideal conditions for small electronic components and the use of PCB terminals.
Maximum design freedom thanks to a generous net area of 6800 mm² on the PCB enables optimum assembly with space-saving geometries of the reflow-capable THR PCB terminal blocks. Error-free assembly and soldering processes are supported by optimized frame geometries and support geometries. In addition, customizable design options such as labeling, color selection and variable printable swivel covers ensure flexibility. Thanks to reflow-compatible connection elements and machine-compatible packaging, maximum efficiency in processing is guaranteed - for time-saving and precise installation.

General ordering data

Type	CH20M6 BC 4P-4P BUS AGY...	Version
Order No.	2771220000	Flange-mounted housing, OMNIMATE Housing - series CH20M Agate
GTIN (EAN)	4064675031956	grey, Housing side panel, Recess in detent foot area for BUS contact,
Qty.	50 ST	Width: 5.2 mm
Type	CH20M6 BC 4P-4P BUS BK ...	Version
Order No.	2771130000	Flange-mounted housing, OMNIMATE Housing - series CH20M
GTIN (EAN)	4064675031864	black, Housing side panel, Recess in detent foot area for BUS contact,
Qty.	50 ST	Width: 5.3 mm
Type	CH20M6 BC 4P-4P BUS GY ...	Version
Order No.	2771140000	Flange-mounted housing, OMNIMATE Housing - series CH20M
GTIN (EAN)	4064675031871	Pebble grey, Housing side panel, Recess in detent foot area for BUS contact, Width: 5.3 mm
Qty.	50 ST	
Type	CH20M6 BC 4P-4P BUS RD ...	Version
Order No.	2771150000	Flange-mounted housing, OMNIMATE Housing - series CH20M
GTIN (EAN)	4064675031888	red, Housing side panel, Recess in detent foot area for BUS contact,
Qty.	50 ST	Width: 5.3 mm
Type	CH20M6 BC 4P-4P BUS TGY...	Version
Order No.	2771170000	Flange-mounted housing, OMNIMATE Housing - series CH20M Traffic
GTIN (EAN)	4064675031901	grey (RAL), Housing side panel, Recess in detent foot area for BUS contact, Width: 5.3 mm
Qty.	50 ST	