



The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 5261 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

The benefits:

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

General ordering data

Version	Mounting tool
Order No.	2748200000
Type	UBH 1/4 E6,3
GTIN (EAN)	4050118895339
Qty.	5 items

Technical data**Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Width	74 mm	Width (inches)	2.9134 inch
Net weight	22 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Bitholder 1/4
------------------------	---------------

Classifications

ETIM 8.0	EC002118	ETIM 9.0	EC002118
ETIM 10.0	EC002118	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		