

HDC MBUS HD 4 F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Version	Data use, 50 V, 10 A, Number of poles: 4, Crimp connection, Female, Required plug-in slots: 0
Order No.	2748580000
Type	HDC MBUS HD 4 F
GTIN (EAN)	4050118890570
Qty.	1 items

HDC MBUS HD 4 F

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	46 mm	Depth (inches)	1.811 inch
Height	15.5 mm	Height (inches)	0.6102 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	32 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

General data

Number of poles	4	UL 94 flammability rating	V-0
Plugging cycles	≥ 500	Type	Female
Surge voltage category	III	Pollution severity	3
Basic material	Polycarbonate	Rated voltage (DIN EN 61984)	50 V
Rated impulse voltage (DIN EN 61984)	0.8 kV	Rated current (DIN EN 61984)	10 A
Required plug-in slots	0		

Version

Type of connection Crimp connection Conductor cross-section, max. 2.5 mm²
 Conductor cross-section, min. 0.14 mm²

Classifications

ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-18
ECLASS 15.0	27-44-02-18		


HDC MBUS HD 4 F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing



Drawing

