

HDC MBUS HS 8 M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Version	Data use, 50 V, 5 A, Number of poles: 8, Crimp connection, Male, Required plug-in slots: 0
Order No.	2748650000
Type	HDC MBUS HS 8 M
GTIN (EAN)	4050118890716
Qty.	1 items

HDC MBUS HS 8 M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	46.2 mm	Depth (inches)	1.8189 inch
Height	16.7 mm	Height (inches)	0.6575 inch
Width	18 mm	Width (inches)	0.7087 inch
Net weight	27.28 g		

Temperatures

Limit temperature -40 °C ... 125 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	fa505316-3e43-4ad0-930c-360dfdbe182a

General data

Number of poles	8	UL 94 flammability rating	V-0
Plugging cycles	≥ 500	Type	Male
Surge voltage category	III	Pollution severity	3
Basic material	Polycarbonate	Series	ModuPlug
Rated voltage (DIN EN 61984)	50 V	Rated impulse voltage (DIN EN 61984)	0.8 kV
Rated current (DIN EN 61984)	5 A	Required plug-in slots	0

PE connection data

Connection type PE Screw connection via module frame

Version

Wire connection cross section AWG, max.	AWG 20	Type of connection	Crimp connection
Wire connection cross section AWG, min.	AWG 28	Conductor cross-section, max.	0.52 mm ²
Conductor cross-section, min.	0.09 mm ²		

Classifications


ETIM 8.0	EC000438	ETIM 9.0	EC000438
ETIM 10.0	EC000438	ECLASS 14.0	27-44-02-18
ECLASS 15.0	27-44-02-18		

HDC MBUS HS 8 M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com



HDC MBUS HS 8 M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Electrical modules




Flexible

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Type	HDC MEMC 2 MC	Version
Order No.	2748560000	Data module, 50 V, 10 A, Number of poles: 2, Crimp connection,
GTIN (EAN)	4050118890730	Male, Required plug-in slots: 2
Qty.	2 ST	

Shield plate MEMC



In addition to heavy-duty connectors, RockStar® includes the appropriate accessories for effective, functional and safe system cabling; e.g. coding systems, shield clamps, cover plates and replacement seals

General ordering data

Type	HDC MEMC ADP	Version
Order No.	2748740000	Shield bus
GTIN (EAN)	4050118890624	
Qty.	1 ST	

D-SUB crimp contacts



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC C HS SM0.08-0.12 AU	Version
Order No.	2748710000	Male, gold, 0.08 - 0.12 mm ²
GTIN (EAN)	4050118890556	
Qty.	100 ST	

HDC MBUS HS 8 M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	HDC C HS SM0.2-0.5 AU	Version	
Order No.	2748700000		Male, gold, 0.2 - 0.5 mm ²
GTIN (EAN)	4050118890709		
Qty.	100 ST		

HDC MBUS HS 8 M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Counterpart

Electrical modules



Flexible

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Type	HDC MBUS HS 8 F	Version	
Order No.	2748640000	Data use, 50 V, 5 A, Number of poles: 8, Crimp connection, Female,	
GTIN (EAN)	4050118890686	Required plug-in slots: 0	
Qty.	1 ST		