

IE-SW-SL10M-7TX-3GC-HV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Features of SubstationLine managed switch series

The SubstationLine includes Ethernet switches complying with the IEC 61850-3 and IEEE 1613 standards, making them robust enough for operation in harsh environments. The family includes variants for mounting on DIN rails and in 19" racks.

All products have a redundant power supply to ensure reliability in critical environments. The new family ranges from managed Fast Ethernet switches to 10-Gigabit Ethernet products with all the necessary features to operate according to the most demanding requirements.

- DIN-rail and 19" rack variants
- IEC 61850-3 and IEEE 1613 compliance
- PRP/HSR support according to Clause 4/Clause 5 of IEC 62439-3
- MMS server based on bridge model defined in IEC 61850-90-4
- Redundant power supply modules in all models
- Wide operating temperature range of -40°C up to 85°C
- Modular switch version with high flexibility in number and type of ports
- Fast/Gigabit/10-Gigabit interfaces
- Layer 3 models for hardware supported routing between up to 28 IP-subnets

General ordering data

Version	Layer 2 Network Switch, managed, Fast/Gigabit Ethernet, IEC 61850-3 / IEEE 1613, high voltage, Number of ports: 7x RJ45 10/100BASE-T(X), 3x combo-ports (10/100/1000BASE-T(X) or 100/1000BaseSFP), IP30, -40 °C...85 °C
Order No.	2778950000
Type	IE-SW-SL10M-7TX-3GC-HV
GTIN (EAN)	4064675048213
Qty.	1 items

IE-SW-SL10M-7TX-3GC-HV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	148.5 mm	Depth (inches)	5.8464 inch
Height	154 mm	Height (inches)	6.063 inch
Width	96.4 mm	Width (inches)	3.7953 inch
Net weight	2000 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl, 7clI
REACH SVHC	Lead 7439-92-1, Lead monoxide 1317-36-8
SCIP	9229992a-00b9-4096-8962-200a7f33e289

EMC conformity and approvals

Free fall	IEC 60870-2-2 class Cm	EMC standards	EN 55032, CISPR 22, EN 61000-3-2, EN 61000-3-3, FCC Part 15 Subpart B Class A, EN 55035, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 3 GHz: 10 V/m, IEC 61000-4-4 EFT: Power: 4 kV; Signal: 4 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8, IEC 61000-4-11
Vibration	IEC 60870-2-2 class Cm and class Bm	Shock	IEC 60870-2-2 class Cm
Safety standard	SELV according to EN 62368-1	Power Transmission & Distribution Systems acc. to standard	IEEE 1613, IEC 61850-3

Environmental conditions

Operating temperature, max.	85 °C	
Operating temperature, min.	-40 °C	
Humidity	5 to 95 % (non-condensing)	
Storage temperature, max.	85 °C	
Storage temperature, min.	-40 °C	
Operating altitude	Altitude, max.	2000 m
	Note	in acc. with UL
	Altitude, max.	6000 m

IE-SW-SL10M-7TX-3GC-HV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Note

for restrictions, see the manufacturer's declaration for operating altitude in section downloads

Guarantee

Time interval 5 years

Interfaces

Fibre-optic ports	100/1000Base SFP Slot	RJ45 ports	10/100BaseT(X) or 10/100/1000BaseT(X), auto negotiation, Full-/half duplex mode, Auto MDI/MDI-X port
Console port interface	RS-232 (RJ45 connector)	Alarm contact	1 relay output with a current capacity of 1 A at 24 V DC
Number of ports	7x RJ45 10/100BASE-T(X), 3x combo-ports (10/100/1000BASE-T(X) or 100/1000BaseSFP)	Function reset button	<5 sec: System reboot, >5 sec: Factory default

MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	599113 h

Management features

Device configuration	Webbrowser (HTTP/HTTPS), SNMP v1/v2c/v3, Local serial console port (RS-232 via RJ-45 port), Upload of a configuration file via web-interface or TFTP-Server, Command Line Interface (Telnet/SSH)	Monitoring function	SNMP v1/v2c/v3, Link Layer Discovery Protocol (LLDP), Port mirroring, Port statistics, Port monitoring, Syslog, RMON (Remote monitoring), Event based warning via E-Mail, Event based warning via relay, Event based warning via SNMP trap
Network redundancy	Spanning Tree Protocol (STP), Rapid Spanning Tree Protocol (RSTP), Multiple Spanning Tree Protocol (MSTP), O-Ring (recovery time <10/30 ms at Fast/Gigabit Ethernet interface), O-Chain (recovery time <10/30 ms at Fast/Gigabit Ethernet interface), Link Aggregation Control Protocol (LACP), Fast recovery	Network traffic filter	Quality of Service (QoS), Class of Service (CoS), Type of Service (ToS), Differentiated Services Code Point (DSCP), Port based VLAN, Tag based VLAN, GVRP (GARP VLAN Registration Protocol), IGMP v2/v3, Multicast VLAN Registration (MVR), Traffic Rate Limiting
IP-address management	Static, DHCP-Client, DHCP-Server (port based, pool-based), DHCP Option 82, DHCP-Relay, IPv4/IPv6	Security functions	VLAN segmentation, Enable/disable ports, TACACS+ and IEEE 802.1X User Authentication, Access control (port based via IEEE 802.1X), Access control list (IP-based), Access control list (MAC-based), Management access security via secure IP-list and configuration of

IE-SW-SL10M-7TX-3GC-HV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Time synchronization management	NTP server, SNTP client	Industrial protocol support	allowed access methods (web-interface, telnet, SSH), Loop protection
			Modbus/TCP slave, PROFINET device acc. to conformance class A

Power supply

Reverse polarity protection	Yes		
Supply voltage	110/220 V DC, 110/220 V AC, 2 redundant isolated inputs		
Overload current protection	Yes		
Connection type	2x 3-pin fork/ring lug connection		
Voltage supply range	Voltage type	DC	
	Voltage, min.	88 V	
	Voltage, max.	373 V	
	Voltage type	AC	
	Voltage, min.	85 V	
	Voltage, max.	264 V	
Current consumption	Voltage	110 V	
	Current	0.18 A	
	Voltage	220 V	
	Current	0.13 A	

Switch characteristics

Priority queues	4	Max. number of available VLANs	4095
VLAN-ID min	1	VLAN-ID max	4094
IGMP-Groups	1024	MAC table size	8 K
Packet buffer size	1 Mbit	Bandwidth backplane	7.4 Gbit/s

Technical data

Housing main material	Metal	Type of mounting	DIN rail
Protection degree	IP30	Speed	Fast/Gigabit Ethernet
Switch	managed		

Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control
Standard	IEEE 802.3 for 10BASE-T, IEEE 802.3u for 100BASE-TX and 100BASE-FX, IEEE 802.3ab for 1000BASE-T, IEEE 802.3z for 1000BASE-X, IEEE 802.3x for flow control, IEEE 802.3ad for port trunk with LACP, IEEE 802.1D for the Spanning Tree protocol, IEEE 802.1w for Rapid STP, IEEE 802.1D-2004 for RSTP:2004 (Rapid Spanning Tree Protocol 2004), IEEE 802.1s for the Multiple Spanning Tree Protocol (MSTP), IEEE 802.1p for Class of Service, IEEE 802.1Q for VLAN tagging, IEEE 802.1X for authentication,		

IE-SW-SL10M-7TX-3GC-HV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

IEEE 802.1AB for Link
Layer Discovery protocol
(LLDP)

Classifications

ETIM 8.0	EC000734	ETIM 9.0	EC000734
ETIM 10.0	EC000734	ECLASS 14.0	19-17-04-01
ECLASS 15.0	19-17-04-01		

IE-SW-SL10M-7TX-3GC-HV

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

SFP transceiver (for use with switches of Eco-, Advanced-, Substation and BasicLine series B)


Features of SFP-Transceiver series

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

General ordering data

Type	IE-SFP-1FE-MM-2	Version
Order No.	2682450000	SFP Transceiver, 100 Mbps, Multimode, LC-Duplex, 4 km, -40 °C...85
GTIN (EAN)	4050118692266	°C
Qty.	1 ST	
Type	IE-SFP-1FE-SM-30	Version
Order No.	2682460000	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 30 km, -40
GTIN (EAN)	4050118692259	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1FE-SM-60	Version
Order No.	2682470000	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 60 km, -40
GTIN (EAN)	4050118692242	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-MM-05	Version
Order No.	2682480000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.5 km, -40
GTIN (EAN)	4050118692235	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-MM-2	Version
Order No.	2682490000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, -40
GTIN (EAN)	4050118692228	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10	Version
Order No.	2682500000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, -40
GTIN (EAN)	4050118692211	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-40	Version
Order No.	2682510000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, -40
GTIN (EAN)	4050118692204	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10-BIDI-T...	Version
Order No.	2682520000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692198	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10-BIDI-T...	Version
Order No.	2682530000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692181	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-20-BIDI-T...	Version
Order No.	2682540000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692174	-40 °C...85 °C
Qty.	1 ST	

IE-SW-SL10M-7TX-3GC-HV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	IE-SFP-1GE-SM-20-BIDI-T...	Version
Order No.	2682550000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692167	-40 °C...85 °C
Qty.	1 ST	

Mounting kit for 19" rack assembly

- For assembling DIN rail-based devices on 19" racks



General ordering data

Type	RM-KIT	Version
Order No.	1241440000	Kit for 19"-rack mounting
GTIN (EAN)	4050118029154	
Qty.	1 ST	