

IE-C5ES8UG0060A44A40-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



General ordering data

| | |
|------------|---|
| Version | System cable, RJ45 IP 67 PushPull V04 plastic, RJ45 IP 20, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), 6 m |
| Order No. | 2757860000 |
| Type | IE-C5ES8UG0060A44A40-X |
| GTIN (EAN) | 4064675005254 |
| Qty. | 1 items |

IE-C5ES8UG0060A44A40-X

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|------------|-------|-----------------|---------------|
| Length | 6 m | Length (inches) | 236.2205 inch |
| Net weight | 257 g | | |

Temperatures

| | | | |
|--------------------------|----------------|-----------------------|--|
| Storage temperature | -40 °C...75 °C | Operating temperature | |
| Installation temperature | -10 °C...60 °C | | |

Environmental Product Compliance

| | |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant |
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 67cf1078-beca-4687-860b-dc475a6ec24a |

Cable specific standards

| | | | |
|------------------------|---------------------------|--|---------------------------------------|
| Standard, assembly | UL-Style 20963 (80°C/30V) | Generic communication cable facilities | ISO / IEC 11801:2002, EN 50173-1:2007 |
| Corrosiveness of fumes | to IEC 60754-2 | | |

Cable structure

| | | | |
|---------------------------------------|--|---------------------------|--|
| Strands | 7 | Sheathing colour | green (RAL 6018) |
| Standard designations | SF/UTP, IE-71C4x2xAWG23/1-PUR 02YSC11Y PIMF | Cross-section | 4*2*AWG 26/7 - 4*2*0.128 mm ² |
| Shielding | SF/UTP | Sheath diameter, max. | 6.3 mm |
| Sheath diameter, min. | 5.7 mm | Arrangement of wire cores | Twisted pair |
| Complete shielding | Aluminium foil, Shielding braid made from copper wiring | Wire material | Stranded tin-plated copper wire |
| Colour sequence or wires - wire pairs | white - blue, white - orange, white - green, white - brown | Shielding braid thickness | 0.1 mm |

Electrical properties of cable

| | | | |
|-----------------|---|--------------------------------|-------------------------|
| Category | Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B) | Capacity at 1 kHz | 47 nF/km |
| Loop resistance | 290 Ω/km | Test voltage: wire-wire-shield | 1000 Vrms, 50 Hz, 1 min |
| Delay skew | 25 ns/100m | Characteristic impedance | 100 ± 5 Ω at 100MHz |

Mechanical and material properties of cable

| | | | |
|--------------------|--|---------------------------------|---------------------|
| Resistance to oils | in accordance with IEC 60811-2-1 | Silicone-free | Yes |
| Halogen | halogen-free, according to IEC 60754-2 | Min. bending radius, repetitive | 10 x cable diameter |

IE-C5ES8UG0060A44A40-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|--------------------------------|--------------------------------|------------------------|----------------|
| Min. bending radius, once only | 4 x cable diameter | Abrasion resistance | very good |
| Resistance to spread of flame | in accordance with IEC 60332-1 | Corrosiveness of fumes | to IEC 60754-2 |

Plug

| | | | |
|------------|---|-----------|---|
| Plug right | RJ45, IP20, male contact, straight, Plastic, shielded | Plug left | RJ45, IP67, male contact, straight, PushPull V04, Plastic, shielded |
|------------|---|-----------|---|

Plug, left

| | |
|-----------|---|
| Plug left | RJ45, IP67, male contact, straight, PushPull V04, Plastic, shielded |
|-----------|---|

Plug, right

| | |
|------------|---|
| Plug right | RJ45, IP20, male contact, straight, Plastic, shielded |
|------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC002599 | ETIM 9.0 | EC002599 |
| ETIM 10.0 | EC002599 | ECLASS 14.0 | 27-06-03-08 |
| ECLASS 15.0 | 27-06-03-08 | | |