

## IE-SWM-SL08-8GESFP

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### Features of SubstationLine managed switch series

The SubstationLine includes Ethernet switches complying with the IEC 61850-3 and IEEE 1613 standards, making them robust enough for operation in harsh environments.

The family includes variants for mounting on DIN rails and in 19" racks.

All products have a redundant power supply to ensure reliability in critical environments. The new family ranges from managed Fast Ethernet switches to 10-Gigabit Ethernet products with all the necessary features to operate according to the most demanding requirements.

- DIN-rail and 19" rack variants
- IEC 61850-3 and IEEE 1613 compliance
- PRP/HSR support according to Clause 4/Clause 5 of IEC 62439-3
- MMS server based on bridge model defined in IEC 61850-90-4
- Redundant power supply modules in all models
- Wide operating temperature range of -40°C up to 85°C
- Modular switch version with high flexibility in number and type of ports
- Fast/Gigabit/10-Gigabit interfaces
- Layer 3 models for hardware supported routing between up to 28 IP-subnets

### General ordering data

Version	Media interface module for modular switch, Fast/Gigabit Ethernet, Number of ports: 8x 100/1000BaseSFP Slot, -40 °C...85 °C
Order No.	<a href="#">2779150000</a>
Type	IE-SWM-SL08-8GESFP
GTIN (EAN)	4064675048510
Qty.	1 items

**Technical data**

**Approvals**

Approvals



ROHS	Conform
UL File Number Search	<a href="#">UL Website</a>
Certificate no. (cULus)	E141197

**Dimensions and weights**

Depth	107 mm	Depth (inches)	4.2126 inch
Height	40.7 mm	Height (inches)	1.6024 inch
Width	99 mm	Width (inches)	3.8976 inch
Net weight	348 g		

**Temperatures**

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

**Environmental Product Compliance**

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	Lead monoxide 1317-36-8

**EMC conformity and approvals**

Safety standard	UL 61010-1, UL 61010-2-201
-----------------	----------------------------

**Environmental conditions**

Operating temperature, max.	85 °C	
Operating temperature, min.	-40 °C	
Humidity	5 to 95 % (non-condensing)	
Storage temperature, max.	85 °C	
Storage temperature, min.	-40 °C	
Operating altitude	Altitude, max.	2000 m
	Note	in acc. with UL
	Altitude, max.	6000 m
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads

**Guarantee**

Time interval	5 years
---------------	---------

**Interfaces**

Fibre-optic ports	100/1000Base SFP Slot	Number of ports	8x 100/1000BaseSFP Slot
-------------------	-----------------------	-----------------	-------------------------

**IE-SWM-SL08-8GESFP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****MTBF**

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	37 12062 h

**Power supply**

Supply voltage via Ethernet switch

**Technical data**

Housing main material	Metal	Type of mounting	Insert in module slot M1,M2,M3
Speed	Fast/Gigabit Ethernet		

**Classifications**

ETIM 8.0	EC000309	ETIM 9.0	EC000309
ETIM 10.0	EC000309	ECLASS 14.0	19-17-03-03
ECLASS 15.0	19-17-03-03		