

CABTITE EP 24/17 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Cabtite - Cable Entry Plates

Insert cables and wires without plugs into control cabinets, enclosures or machines in the smallest of spaces, easily and in a space-saving manner.

With the Cabtite cable entry plates, you can do this even in harsh environments, whether protective hoses, pneumatic/hydraulic hoses or fiber optic cables - you can install your cables quickly, easily and in a space-saving manner. The installation is done through only one rectangular wall cut-out and is therefore up to 40% faster in the installation time (compared to standard cable glands).

The IP66 screw version of cable entry plates are tested according to DIN EN 60529 and made of UL94 V-0 certified TPE material with hard plastic core, suitable for the temperature range from -40°C to +90°C.

Cabtite cable entry plates are an economical alternative to conventional cable glands.

General ordering data

Version	Cable entry plate, Cabtite (cable entry system), TPE, grey, Height: 58 mm, Width: 149.6 mm, Depth: 20.2 mm, -40 °C...90 °C, IP66
Order No.	2779350000
Type	CABTITE EP 24/17 GY
GTIN (EAN)	4064675048923
Qty.	10 items

CABTITE EP 24/17 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E223801

Dimensions and weights

Depth	20.2 mm	Depth (inches)	0.7953 inch
Height	58 mm	Height (inches)	2.2835 inch
Width	149.6 mm	Width (inches)	5.8898 inch
Net weight	108.1 g		

Temperatures

Operating temperature	-40 °C...90 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Tightening torque	3.5 Nm	Silicone	No
UL 94 flammability rating	V-0	Protection degree	IP66
Basic material	TPE	Protection class (UL)	Type 1, Type 12, Type 4X

Number of connectable cables

Type of mounting	4 screws		
Number of connectable cables	17		
Cable entries	Number	4	
	Cable diameter, min.	3.2 mm	
	Cable diameter, max.	6.3 mm	
	Cable type	Round cable	
	Number	2	
	Cable diameter, min.	4 mm	
	Cable diameter, max.	7.5 mm	
	Cable type	Round cable	
	Number	1	
	Cable diameter, min.	5.5 mm	
	Cable diameter, max.	10.5 mm	
	Cable type	Round cable	
	Number	10	
	Cable diameter, min.	8 mm	
	Cable diameter, max.	12.5 mm	
Cable type	Round cable		

Classifications

ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 14.0	27-18-28-15

CABTITE EP 24/17 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Technical data

www.weidmueller.com

ECLASS 15.0

27-18-28-15

CABTITE EP 24/17 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

