Data sheet

SAIH-PB-2X0.34-PVC-100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Weidmüller offers a large and comprehensive range of sensor-actuator cables. We provide both, sensor cables as well as bus and valve cables of various sizes and lengths. If you cannot find a specific product or a product in the desired length, just contact us.

General ordering data

Version	Bus line, Number of poles: 2, 100 m, Shielded: Yes, LED: No, Sheath material: PVC, Halogen: No
Order No.	2764910000
Type	SAIH-PB-2X0.34-PVC-100
GTIN (EAN)	4064675031154
Qty.	1 items
Packaging	on plastic reel
Delivery status	This article will no longer be available in the future.
Last order date	2027-03-31T00:00:00+02:00

Data sheet

SAIH-PB-2X0.34-PVC-100

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform

Dimensions and weights

Net weight	60 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical specifications for cable

Cable length	100 m	Sheathing colour	violet
Resistance to oils	Yes	Suitable for cable carriers	No
Core cross-section	0.34 mm²	Number of wires	2
Shielded	Yes	Halogen	No
Insulation	TPM, PVC	Bending radius, min., moving	9 x cable diameter
Bending radius, min., stationary	18 x cable diameter	Sheath material	PVC
Welding spark resistance	No	Colour coding	red, green
Torsion resistance	0 °/m	Temperature range, stationary	-20...70 °C
Resistant to welding beads	No	Temperature range, moving	-5...60 °C
Number of poles	2	Outside diameter	7.8 mm ± 0.2 mm

Cable structure

Sheathing colour	violet	Number of wires	2
Insulation	TPM, PVC	Material sheath	PVC
Colour coding	red, green		

Electrical properties of cable

Category	Miscellaneous

Mechanical and material properties of cable

Resistance to oils	Yes	Colour	red, green
Halogen	No	Torsion resistance	0 °/m

Classifications

ETIM 8.0	EC003249	ETIM 9.0	EC003249
ETIM 10.0	EC003249	ECLASS 14.0	27-06-18-01
ECLASS 15.0	27-06-18-01		