

**IE-ANT-CELL-SISO-LO-NF****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

**General ordering data**

Version	Omni-directional antenna, Cellular antenna, Up to 5G (NR), Vertical, N female, IP66, Impedance: 50 $\Omega$
Order No.	<a href="#">2788150000</a>
Type	IE-ANT-CELL-SISO-LO-NF
GTIN (EAN)	4064675066415
Qty.	1 items

## IE-ANT-CELL-SISO-LO-NF

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Approvals

ROHS	Conform
------	---------

### Dimensions and weights

Height	89 mm	Height (inches)	3.5039 inch
Diameter	35.8 mm	Net weight	263.02 g

### Temperatures

Storage temperature	-40 °C...70 °C	Operating temperature	-40 °C...70 °C
---------------------	----------------	-----------------------	----------------

### Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	e4cad7fc-a55e-4d5c-8f05-417a6385e9b6

### Enclosure material

Colour	black
--------	-------

### Included in delivery

Included in delivery	1 x antenna
----------------------	-------------

### Technical data

Type of connection	N female	Impedance	50 Ω
Standing wave ratio	< 2.0 typical, 2.5 max.	Composite power max.	150 W
Frequency range	690-950 MHz, 1.7-3.8 GHz	Antenna gain	3 dBi
Polarisation	Vertical		

### Environmental conditions

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-40 °C

### Classifications

ETIM 8.0	EC001698	ETIM 9.0	EC001698
ETIM 10.0	EC001698	ECLASS 14.0	19-07-01-07
ECLASS 15.0	19-07-01-07		

## IE-ANT-CELL-SISO-LO-NF

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

### Antennas and antenna accessories (coax cables and mounts)



Antennas and antenna accessories (coax cables and mounts)

- State-of-the-art antennas
- Industry proven
- Robust design (up to IP67 protection)
- For outdoor and indoor use
- Latest technology support
- Up to Wi-Fi 6 and Wi-Fi 6E (2.4 GHz, 5 GHz, 6 GHz)
- Up to 5G (NR) support (700 MHz - 3.8 GHz)
- Also support for other technologies (e.g. Bluetooth, GNSS, etc.)
- Appropriate coax cables at different lengths
- Suitable pole and wall mounts

### General ordering data

Type	IE-ANT-MOUNT-POLE-NF	Version
Order No.	<a href="#">2788470000</a>	Antenna mount for "IE-ANT-WL-DB-SISO-LO-NF", "IE-ANT-CELL-SISO-LO-NF"
GTIN (EAN)	4064675066477	
Qty.	1 ST	
Type	IE-CC-NM-SMAM-1M	Version
Order No.	<a href="#">2788010000</a>	Antenna cable, Connection 1.: N male, Connection 2.: SMA male,
GTIN (EAN)	4064675066279	Length: 1 m
Qty.	1 ST	
Type	IE-CC-NM-SMAM-2M	Version
Order No.	<a href="#">1491180000</a>	Antenna cable, Connection 1.: N male, Connection 2.: SMA male,
GTIN (EAN)	4050118300741	Length: 2 m
Qty.	1 ST	
Type	IE-CC-NM-SMAM-3M	Version
Order No.	<a href="#">2788020000</a>	Antenna cable, Connection 1.: N male, Connection 2.: SMA male,
GTIN (EAN)	4064675066286	Length: 3 m
Qty.	1 ST	
Type	IE-CC-NM-SMAM-4M	Version
Order No.	<a href="#">1491190000</a>	Antenna cable, Connection 1.: N male, Connection 2.: SMA male,
GTIN (EAN)	4050118300734	Length: 4 m
Qty.	1 ST	
Type	IE-CC-NM-SMAM-5M	Version
Order No.	<a href="#">2788030000</a>	Antenna cable, Connection 1.: N male, Connection 2.: SMA male,
GTIN (EAN)	4064675066293	Length: 5 m
Qty.	1 ST	
Type	IE-CC-NM-SMAM-6M	Version
Order No.	<a href="#">1491210000</a>	Antenna cable, Connection 1.: N male, Connection 2.: SMA male,
GTIN (EAN)	4050118300758	Length: 6 m
Qty.	1 ST	