


THM ET 200SP-HA 18.8/50 TU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

General ordering data

Version	THM, Device markers, 18.8 x 50 mm, Siemens, Turquoise
Order No.	2799210000
Type	THM ET 200SP-HA 18.8/50 TU
GTIN (EAN)	4064675260967
Qty.	1500 items

THM ET 200SP-HA 18.8/50 TU

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.0031 inch
Height	18.8 mm	Height (inches)	0.7402 inch
Width	50 mm	Width (inches)	1.9685 inch
Net weight	0.07 g		

Temperatures

Operating temperature range	-50...100 °C
-----------------------------	--------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General data

Version	Self-adhesive	
Width	50 mm	
UL 94 flammability rating	HB	
Operating temperature range, max.	100 °C	
Operating temperature range, min.	-50 °C	
Colour	Turquoise	
Halogen	No	
Basic material	Polypropylene	
Printed characters	without	
Number of markers per packaging unit	Form of supply	Label reel
Approval acc. to UL 969 compatible printer	No	
Number of markers per combination	1 Label reel = Device markers	
Operating temperature range	-50...100 °C	
Application/manufacturer	Siemens	

Device markers

Halogen	No
---------	----

Classifications

ETIM 8.0	EC001288	ETIM 9.0	EC001288
ETIM 10.0	EC001288	ECLASS 14.0	27-28-11-04
ECLASS 15.0	27-28-11-04		

