


**BLZ 7.62/04/180 SN GN BX**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)


Female plugs with clamping-yoke screw wire-connect system. The female plugs provide space for labelling and can be coded.

**General ordering data**

|              |   |
|--------------|---|
| Version      | PCB plug-in connector, female plug, 7.62 mm, Number of poles: 4, 180°, Clamping yoke connection, Clamping range, max. : 3.31 mm², Box |
| Order No.    | <a href="#">2775030000</a>  |
| Type         | BLZ 7.62/04/180 SN GN BX  |
| GTIN (EAN)   | 4064675040040   |
| Qty.         | 100 items   |
| Product data | IEC: 800 V / 18,5 A / 0.2 - 2.5 mm²<br>UL: 300 V / 15 A / AWG 26 - AWG 12   |
| Packaging    | Box   |

## BLZ 7.62/04/180 SN GN BX

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |             |
|------------|----------|-----------------|-------------|
| Depth      | 20.1 mm  | Depth (inches)  | 0.7913 inch |
| Height     | 15.2 mm  | Height (inches) | 0.5984 inch |
| Width      | 30.48 mm | Width (inches)  | 1.2 inch    |
| Net weight | 7.64 g   |                 |             |

## Environmental Product Compliance

|                          |                             |                  |  |
|--------------------------|-----------------------------|------------------|--|
| RoHS Compliance Status   | Compliant without exemption |                  |  |
| REACH SVHC               | No SVHC above 0.1 wt%       |                  |  |
| Product Carbon Footprint | Cradle to gate              | 0.191 kg CO2 eq. |  |

## System Parameters

|                            |                                     |  |                          |
|----------------------------|-------------------------------------|--|--------------------------|
| Product family             | OMNIMATE Signal - series BL/SL 7.62 | Wire connection method                       | Clamping yoke connection |
| Pitch in mm (P)            | 7.62 mm                             | Pitch in inches (P)                          | 0.300 "                  |
| Conductor outlet direction | 180°                                | Number of poles                              | 4                        |
| L1 in mm                   | 22.86 mm                            | L1 in inches                                 | 0.900 "                  |
| Pin series quantity        | 1                                   | Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch   |
| Volume resistance          | 4.50 mΩ                             | Can be coded                                 | Yes                      |
| Tightening torque, min.    | 0.4 Nm                              | Tightening torque, max.                      | 0.5 Nm                   |
| Clamping screw             | M 2.5                               | Screwdriver blade standard                   | DIN 5264                 |
| Plugging cycles            | 25                                  | Pulling force/pole, max.                     | 2 N                      |

## Material data

|                                  |          |                             |            |
|----------------------------------|----------|-----------------------------|------------|
| Insulating material              | PBT      | Colour                      | Pale green |
| Colour chart (similar)           | RAL 6021 | Insulating material group   | Illa       |
| Comparative Tracking Index (CTI) | ≥ 200    | Moisture Level (MSL)        |            |
| UL 94 flammability rating        | V-0      | Contact material            | Cu-alloy   |
| Storage temperature, min.        | -40 °C   | Storage temperature, max.   | 70 °C      |
| Operating temperature, min.      | -50 °C   | Operating temperature, max. | 100 °C     |

## Conductors suitable for connection

|   |                         |   |  |
|---|-------------------------|---|--|
| Clamping range, min.  | 0.13 mm <sup>2</sup>    | Clamping range, max.  | 3.31 mm <sup>2</sup>   |
| Solid, min. H05(07) V-U   | 0.2 mm <sup>2</sup>     | Solid, max. H05(07) V-U   | 2.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K  | 0.2 mm <sup>2</sup>     | Flexible, max. H05(07) V-K  | 2.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, 0.2 mm <sup>2</sup> min. |                         | w. plastic collar ferrule, DIN 46228 pt 4, 2.5 mm <sup>2</sup> max. |  |
| w. wire end ferrule, DIN 46228 pt 1, 0.2 mm <sup>2</sup> min.       |                         | w. wire end ferrule, DIN 46228 pt 1, 2.5 mm <sup>2</sup> max.       |  |
| Plug gauge in accordance with EN 60999 a x b; ø                     | 2.8 mm x 2.0 mm; 2.4 mm | Reference text  | The outside diameter of the plastic collar should not be larger than the pitch (P). Length of ferrules is to be chosen depending on the product and the rated voltage. |

## Rated data acc. to IEC

|   |                        |   |        |
|---|------------------------|---|--------|
| tested acc. to standard                       | IEC 60664-1, IEC 61984 | Rated current, min. number of poles (Tu=20°C) | 18.5 A |
| Rated current, max. number of poles (Tu=20°C) | 17 A                   | Rated current, min. number of poles (Tu=40°C) | 15 A   |

## BLZ 7.62/04/180 SN GN BX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

### Technical data

|   |        |   |                   |
|---|--------|---|-------------------|
| Rated current, max. number of poles (Tu=40°C)                             | 14.5 A | Rated voltage for surge voltage class / pollution degree II/2         | 800 V             |
| Rated voltage for surge voltage class / pollution degree III/2            | 630 V  | Rated voltage for surge voltage class / pollution degree III/3        | 500 V             |
| Rated impulse voltage for surge voltage class/ pollution degree II/2      | 6000 V | Rated impulse voltage for surge voltage class/ pollution degree III/2 | 6 kV              |
| Rated impulse voltage for surge voltage class/ contamination degree III/3 | 6 kV   | Short-time withstand current resistance                               | 3 x 1s with 120 A |

#### Rated data acc. to CSA

|                                   |        |                                   |        |
|-----------------------------------|--------|-----------------------------------|--------|
| Rated voltage (Use group B / CSA) | 300 V  | Rated voltage (Use group D / CSA) | 300 V  |
| Rated current (Use group B / CSA) | 15 A   | Rated current (Use group D / CSA) | 10 A   |
| Wire cross-section, AWG, min.     | AWG 26 | Wire cross-section, AWG, max.     | AWG 12 |

#### Rated data acc. to UL 1059

|                                       |        |                                       |        |
|---------------------------------------|--------|---------------------------------------|--------|
| Rated voltage (Use group B / UL 1059) | 300 V  | Rated voltage (Use group D / UL 1059) | 300 V  |
| Rated current (Use group B / UL 1059) | 15 A   | Rated current (Use group D / UL 1059) | 10 A   |
| Wire cross-section, AWG, min.         | AWG 26 | Wire cross-section, AWG, max.         | AWG 12 |

#### Packing

|           |           |            |           |
|-----------|-----------|------------|-----------|
| Packaging | Box       | VPE length | 161.00 mm |
| VPE width | 141.00 mm | VPE height | 85.00 mm  |

#### Important note


IPC conformity      Conformity: The products are developed, manufactured and delivered according international recognized standards and norms and comply with the assured properties in the data sheet resp. fulfill decorative properties in accordance with IPC-A-610 "Class 2". Further claims on the products can be evaluated on request.

- Notes
- Additional variants on request
  - Gold-plated contact surfaces on request
  - Rated current related to rated cross-section & min. No. of poles.
  - Wire end ferrule without plastic collar to DIN 46228/1
  - Wire end ferrule with plastic collar to DIN 46228/4
  - P on drawing = pitch
  - Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
  - In accordance with IEC 61984, OMNIMATE-connectors are connectors without breaking capacity (COC). During designated use, connectors are not allowed to be engaged or disengaged when live or under load
  - Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

#### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002638    | ETIM 9.0    | EC002638    |
| ETIM 10.0   | EC002638    | ECLASS 14.0 | 27-46-02-02 |
| ECLASS 15.0 | 27-46-02-02 |             |             |

Dimensional drawing



Derating curve

