

IE-SWM-SL08-8GT

Weidmüller Interface GmbH & Co. KG

Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Features of SubstationLine managed switch series

The SubstationLine includes Ethernet switches complying with the IEC 61850-3 and IEEE 1613 standards, making them robust enough for operation in harsh environments. The family includes variants for mounting on DIN rails and in 19" racks.

All products have a redundant power supply to ensure reliability in critical environments. The new family ranges from managed Fast Ethernet switches to 10-Gigabit Ethenet products with all the necessary features to operate according to the most demanding requirements.

- DIN-rail and 19" rack variants
- IEC 61850-3 and IEEE 1613 compliance
- PRP/HSR support according to Clause 4/Clause 5 of IEC 62439-3
- MMS server based on bridge model defined in IEC 61850-90-4
- Redundant power supply modules in all models
- Wide operating temperature range of -40°C up to 85°C
- Modular switch version with high flexibility in number and type of ports
- Fast/Gigabit/10-Gigabit interfaces
- Layer 3 models for hardware supported routing between up to 28 IP-subnets

General ordering data

Version	Media interface module for modular switch, Fast/Gigabit Ethernet, Number of ports: 8x RJ45, -40 °C...85 °C
Order No.	2779140000
Type	IE-SWM-SL08-8GT
GTIN (EAN)	4064675048503
Qty.	1 items

IE-SWM-SL08-8GT

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Dimensions and weights

Depth	107 mm	Depth (inches)	4.2126 inch
Height	40.7 mm	Height (inches)	1.6024 inch
Width	99 mm	Width (inches)	3.8976 inch
Net weight	348 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7a, 7cl
REACH SVHC	Lead 7439-92-1, Lead monoxide 1317-36-8
SCIP	36ea5127-94bd-4ebc-ad9a-a6743a4f064f

EMC conformity and approvals

Safety standard	UL 61010-1, UL 61010-2-201
-----------------	----------------------------

Environmental conditions

Operating temperature, max.	85 °C								
Operating temperature, min.	-40 °C								
Humidity	5 to 95 % (non-condensing)								
Storage temperature, max.	85 °C								
Storage temperature, min.	-40 °C								
Operating altitude	<table> <tr> <td>Altitude, max.</td> <td>2000 m</td> </tr> <tr> <td>Note</td> <td>in acc. with UL</td> </tr> <tr> <td>Altitude, max.</td> <td>6000 m</td> </tr> <tr> <td>Note</td> <td>for restrictions, see the manufacturer's declaration for operating altitude in section downloads</td> </tr> </table>	Altitude, max.	2000 m	Note	in acc. with UL	Altitude, max.	6000 m	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads
Altitude, max.	2000 m								
Note	in acc. with UL								
Altitude, max.	6000 m								
Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads								

Guarantee

Time interval	5 years
---------------	---------

Interfaces

RJ45 ports	10/100/1000BaseT(X), auto negotiation, Full-/half-	Number of ports	8x RJ45
------------	--	-----------------	---------

IE-SWM-SL08-8GT

Weidmüller Interface GmbH & Co. KG
Klingenbergsstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

duplex mode, Auto MDI/
MDI-X port

MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	1303990 h

Power supply

Supply voltage	via Ethernet switch
----------------	---------------------

Technical data

Housing main material	Metal	Type of mounting	Insert in module slot M1,M2,M3
Speed	Fast/Gigabit Ethernet		

Classifications

ETIM 8.0	EC000309	ETIM 9.0	EC000309
ETIM 10.0	EC000309	ECLASS 14.0	19-17-03-03
ECLASS 15.0	19-17-03-03		