

IE-SWM-SL08-8GESFP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Features of SubstationLine managed switch series

The SubstationLine includes Ethernet switches complying with the IEC 61850-3 and IEEE 1613 standards, making them robust enough for operation in harsh environments.

The family includes variants for mounting on DIN rails and in 19" racks.

All products have a redundant power supply to ensure reliability in critical environments. The new family ranges from managed Fast Ethernet switches to 10-Gigabit Ethernet products with all the necessary features to operate according to the most demanding requirements.

- DIN-rail and 19" rack variants
- IEC 61850-3 and IEEE 1613 compliance
- PRP/HSR support according to Clause 4/Clause 5 of IEC 62439-3
- MMS server based on bridge model defined in IEC 61850-90-4
- Redundant power supply modules in all models
- Wide operating temperature range of -40°C up to 85°C
- Modular switch version with high flexibility in number and type of ports
- Fast/Gigabit/10-Gigabit interfaces
- Layer 3 models for hardware supported routing between up to 28 IP-subnets

General ordering data

Version	Media interface module for modular switch, Fast/Gigabit Ethernet, Number of ports: 8x 100/1000BaseSFP Slot, -40 °C...85 °C
Order No.	2779150000
Type	IE-SWM-SL08-8GESFP
GTIN (EAN)	4064675048510
Qty.	1 items

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Dimensions and weights

Depth	107 mm	Depth (inches)	4.2126 inch
Height	40.7 mm	Height (inches)	1.6024 inch
Width	99 mm	Width (inches)	3.8976 inch
Net weight	348 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Humidity	5 to 95 % (non-condensing)		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	7cl
REACH SVHC	Lead monoxide 1317-36-8
SCIP	e2394c23-eb5e-4fbc-aae0-3075b2f73abf

EMC conformity and approvals

Safety standard	UL 61010-1, UL 61010-2-201
-----------------	----------------------------

Environmental conditions

Operating temperature, max.	85 °C	
Operating temperature, min.	-40 °C	
Humidity	5 to 95 % (non-condensing)	
Storage temperature, max.	85 °C	
Storage temperature, min.	-40 °C	
Operating altitude	Altitude, max.	2000 m
	Note	in acc. with UL
	Altitude, max.	6000 m
	Note	for restrictions, see the manufacturer's declaration for operating altitude in section downloads

Guarantee

Time interval	5 years
---------------	---------

Interfaces

Fibre-optic ports	100/1000Base SFP Slot	Number of ports	8x 100/1000BaseSFP Slot
-------------------	-----------------------	-----------------	-------------------------

IE-SWM-SL08-8GESFP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

MTBF

MTBF	According to Standard	Telcordia SR-332
	Operating time (hours), min.	37 12062 h

Power supply

Supply voltage via Ethernet switch

Technical data

Housing main material	Metal	Type of mounting	Insert in module slot M1,M2,M3
Speed	Fast/Gigabit Ethernet		

Classifications

ETIM 8.0	EC000309	ETIM 9.0	EC000309
ETIM 10.0	EC000309	ECLASS 14.0	19-17-03-03
ECLASS 15.0	19-17-03-03		

IE-SWM-SL08-8GESFP

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

SFP transceiver (for use with switches of Eco-, Advanced-, Substation and BasicLine series B)


Features of SFP-Transceiver series

- Huge variety of transceiver types for several transmission speeds (up to 10 Gigabit Ethernet) and distances (up to 60 km)
- BiDi SFP models for communication via single fiber
- Easy control of transceiver status due to support of Digital Diagnostic Monitoring (DDM)
- Hot pluggable (during operation)
- Class 1 laser product, EN60825-1 compliant
- Applicable for switches of the Eco-, Advanced- and SubstationLine

General ordering data

Type	IE-SFP-1FE-MM-2	Version
Order No.	2682450000	SFP Transceiver, 100 Mbps, Multimode, LC-Duplex, 4 km, -40 °C...85
GTIN (EAN)	4050118692266	°C
Qty.	1 ST	
Type	IE-SFP-1FE-SM-30	Version
Order No.	2682460000	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 30 km, -40
GTIN (EAN)	4050118692259	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1FE-SM-60	Version
Order No.	2682470000	SFP Transceiver, 100 Mbps, Singlemode, LC-Duplex, 60 km, -40
GTIN (EAN)	4050118692242	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-MM-05	Version
Order No.	2682480000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 0.5 km, -40
GTIN (EAN)	4050118692235	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-MM-2	Version
Order No.	2682490000	SFP Transceiver, 1000 Mbps, Multimode, LC-Duplex, 2 km, -40
GTIN (EAN)	4050118692228	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10	Version
Order No.	2682500000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 10 km, -40
GTIN (EAN)	4050118692211	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-40	Version
Order No.	2682510000	SFP Transceiver, 1000 Mbps, Singlemode, LC-Duplex, 40 km, -40
GTIN (EAN)	4050118692204	°C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10-BIDI-T...	Version
Order No.	2682520000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692198	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-10-BIDI-T...	Version
Order No.	2682530000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 10 km,
GTIN (EAN)	4050118692181	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-SM-20-BIDI-T...	Version
Order No.	2682540000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692174	-40 °C...85 °C
Qty.	1 ST	

IE-SWM-SL08-8GESFP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	IE-SFP-1GE-SM-20-BIDI-T...	Version
Order No.	2682550000	SFP Transceiver, 1000 Mbps, Singlemode BiDi, LC-Simplex, 20 km,
GTIN (EAN)	4050118692167	-40 °C...85 °C
Qty.	1 ST	
Type	IE-SFP-1GE-RJ45	Version
Order No.	2766120000	SFP Transceiver, 10/100/1000 MBit/s, RJ45, 0.1 km, -40 °C...85 °C
GTIN (EAN)	4064675023791	
Qty.	1 ST	