

**SAIBGI-M-4D-5/9.7-M12-WDF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



M12 plug-in connector in IP 67 available with crew or tension clamp connection

**General ordering data**

Version	Field attachable connector, M12
Order No.	<a href="#">2783150000</a>
Type	SAIBGI-M-4D-5/9.7-M12-WDF
GTIN (EAN)	4064675059875
Qty.	1 items

## SAIBGI-M-4D-5/9.7-M12-WDF

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

Diameter 16.8 mm Net weight 30 g

## Environmental Product Compliance

RoHS Compliance Status Compliant  
REACH SVHC No SVHC above 0.1 wt%

## Technical data customisable plug-in connectors

Number of poles	4	Coding	D-coded
Contact surface	Gold-plated	LED	No
Type of connection	Insulation displacement connection	Housing main material	zinc diecast nickel-plated
Insulation resistance	≥ 100 MΩ	Cable diameter, max.	9.7 mm
Cable diameter, min.	5 mm	Category	Cat. 5e
Conductor cross-section, max.	0.34 mm <sup>2</sup>	Conductor cross-section, min.	0.14 mm <sup>2</sup>
Nominal voltage	250 V	Nominal current	4 A
Protection degree	IP67	Plugging cycles	≥ 100
Pollution severity	2	Gender of contact	Female
Shield connection	Yes	Threaded ring material	Diecast zinc
Temperature range of housing	-40 ... +85 °C		

## General Info

Number of poles	4	Connection 1	M12
Connection 2	IDC	UL 94 flammability rating	V-0
Housing main material	zinc diecast nickel-plated	Insulation cross-section, min.	0.85 mm
Insulation cross-section, max.	1.6 mm	Category	Cat. 5e
Connection thread	M12	Contact surface	Gold-plated
Wire connection diameter, solid, min.	0.51 mm	Wire connection diameter, solid, max.	0.64 mm
Wire cross-section, solid, min. (AWG)	AWG 24	Wire cross-section, solid, max. (AWG)	AWG 22
Wire connection diameter, flexible, min.	0.48 mm	Wire connection diameter, flexible, max.	0.76 mm
Wire connection cross section, finely stranded, min.	0.14 mm <sup>2</sup>	Wire connection cross section, finely stranded, max.	0.36 mm <sup>2</sup>
Wire cross-section, solid, min.	0.2 mm <sup>2</sup>	Wire cross-section, solid, max.	0.32 mm <sup>2</sup>
Wire cross-section, finely stranded, min. (AWG)	AWG 26	Wire cross-section, finely stranded, max. (AWG)	AWG 22
Protection degree	IP67	Plugging cycles	≥ 100

## Electrical properties

Insulation resistance ≥ 100 MΩ Nominal voltage 250 V

## General standards

Connector standard IEC 61076-2-101

**SAIBGI-M-4D-5/9.7-M12-WDF**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Technical data****Standards**

Connector standard	IEC 61076-2-101
--------------------	-----------------

**Classifications**

ETIM 8.0	EC002635	ETIM 9.0	EC002635
ETIM 10.0	EC002635	ECLASS 14.0	27-44-01-16
ECLASS 15.0	27-44-01-16		


**SAIBGI-M-4D-5/9.7-M12-WDF**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Drawings**

**Dimensioned drawing**



**Pinning**

M12 plug

